


D

C

B

A



LC CONN. MARK		LC CONN. MARK
A	↔	B
B	↔	A

NOTES:

- 1ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm
ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2RETURN LOSS ≥ 25 dB, IN MATED CONDITION
AGAINST REFERENCE CONNECTOR AT 850 nm
- 3TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
- 4CABLE INFORMATION:

— CORE DIAMETER:50/125 μm

— OUTER JACKET DIAMETER:1.8x3.6 mm

— OUTER JACKET COLOUR:AQUA

— OUTER JACKET MATERIAL:LSZH
- 5BLANK LABEL

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	”L” (meter)
X-2061311-Y	XY.0

2	BLANK LABEL			3							
2	LC DUPLEX CONNECTOR, MULTI MODE, BEIGE			2							
L	FOCAB 1.8MZ 50/125 OM3, AQUA, LSZH			1							
Qty	Description			Item							
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN CHK A. HENGELMOLEN APVD A. HENGELMOLEN	16OCT2009 16OCT2009 16OCT2009								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		Tyco Electronics Corporation s—Hertogenbosch, Nederland							
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME								
	PRODUCT SPEC		FIBER OPTIC LEAD 1.8MZ LC/DPX – LC/DPX MULTI MODE 50/125 OM3								
	APPLICATION SPEC										
MATERIAL	FINISH	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
—	—	—	—	A2	00779	C=2061311	—				
CUSTOMER DRAWING						SCALE	NTS	SHEET	1 of 1	REV	A