

Features

LED DRIVER

- Universal AC Input
- Constant Voltage / Constant Current Operation
- Active Power Factor Correction
- IP67 Design for Indoor and Outdoor Use
- Cooling by Free Air Convection
- PSE Certified for Japan market

Description

The RACD150-PSE LED driver series offer 150W of power with an universal input voltage range of 90-130VAC and constant current output up to 11A at a voltage of approximately 12V. The series feature a unique dual mode operation for either constant current or constant voltage making them suitable for driving LEDs directly or via local constant-current DC/DC modules directly on the light engine board.

The RACD150-PSE series are fully sealed IP67 LED drivers and therefore ideally suited for indoor and outdoor applications including road, street and walkway lighting, high-bay, LED signage, and outdoor area lighting for car parks, public buildings and tunnels. The LED drivers are PSE certified and come with a 5 year warranty.

Selection Guide

Part Number	CV Mode		CC Mode		Efficiency (115VAC) (typ.)
	Constant Voltage (V)	Current Range (A)	DC Voltage Range (V)	Constant Current (A)	
RACD150-12-PSE	12	0-11	9-12	11	85%
RACD150-24-PSE	24	0-6.3	14-24	6.3	87%
RACD150-36-PSE	36	0-4.2	26-36	4.2	90%
RACD150-48-PSE	48	0-3.2	34-48	3.2	90%

Specifications

Input Voltage Range			90-130 VAC
Input Frequency Range			47-63Hz
Power Factor	Full Load, 115VAC	>0.98	
THD	Full Load, 115VAC	8% max.	
AC Current	115VAC	2A max.	
Input / Output Isolation			3.75kVAC / 1 minute
Input / Case Isolation			1.8kVAC / 1 minute
Output / Case Isolation			0.5kVAC / 1 minute
Leakage Current			<0.5mA
Current Tolerance			±5%
Voltage Tolerance			-1% to 5%
Start-up Time	Full Load, 115VAC	1.0s	
Ripple & Noise (at 20MHz bandwidth)			150mVp-p max.
Over Current Protection	95%-105% rated current	Auto-Recovery	
Short Circuit Protection			Hiccup Mode
Over Voltage Protection	12V	12.5V typ.	
Latch Mode	24V	24.5V typ.	
(Power off to recover)	36V	36.5V typ.	
	48V	48.5V typ.	
Over Temperature Protection			Tcase 95°C ±10°C
Operating Temperature Range (free air convection, according to PSE)	without derating	-20°C to +50°C (see graph)	
	Case Temperature	75°C max.	
Operation Humidity			20%-90% RH Non-Condensing
Storage Temperature			-40°C to +80°C
Storage Humidity			10%-90% RH
Vibration			10-500Hz, 2G, 60 Min. along X, Y and Z
IP Rating			IP67
EMC Standards (designed to meet)	EMC Compatibility	EN55015 FCC, Part 15	
	Harmonic Current	EN61000-3-2 Class C (≥75% load) EN61000-3-3	
	EMC Immunity	EN61000-4-2, 3, 4, 5, 6, 11	

continued on next Page

LIGHTLINE

AC/DC-Converter

with 5 Year Warranty

RECOM

150 Watt Single Output



RACD150-PSE

Note:

All LED Drivers may not be used without a load. They must be switched on the primary side only. Noncompliance may damage the LED or reduce its lifetime.



Refer to Application Notes

Specifications

Dimension		199.2*68*39mm
Weight		1080g
MTBF	using MIL-HDBK-217F (25°C)	200 x 10 ³ hours
Design Lifetime		70 x 10 ³ hours


The use of a circuit breaker with C-characteristic is recommended.

Derating Curve




Characteristics

Constant Voltage / Constant Current Curve



Package Style and Pinning



The product information and specifications are subject to change without prior notice. All products are designed for non-safety critical commercial and industrial applications. The Buyer agrees to implement safeguards that anticipate the consequences of any failures that might cause harm, loss of life and/or damage property.