

RING WRENCHES

Metric - Bihexagon

Ref.	A mm	D				T				C		L		Wt. kg
		Small end		Large end		Small end		Large end		mm	in	mm	in	
		mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	
9RBM557	5.5 x 7	10.2	0.40	11.7	0.46	5.6	0.22	5.6	0.22	11.1	0.44	114	4 1/2	0.03
9RBM67	6 x 7	10.7	0.42	12.2	0.48	5.6	0.22	5.6	0.22	11.1	0.44	114	4 1/2	0.03
9RBM89	8 x 9	13.6	0.53	15.0	0.59	6.4	0.25	6.4	0.25	12.7	0.50	152	6	0.05
9RBM101	8 x 10	13.6	0.53	16.4	0.65	6.4	0.25	6.4	0.25	12.7	0.50	152	6	0.05
9RBM1011	10 x 11	16.4	0.65	17.8	0.70	6.4	0.25	7.1	0.28	12.7	0.50	152	6	0.05
9RBM1013	10 x 13	16.4	0.65	20.6	0.81	6.4	0.25	7.9	0.31	15.9	0.62	178	7	0.09
9RBM1213	12 x 13	19.2	0.76	20.6	0.81	7.9	0.31	7.9	0.31	15.9	0.62	178	7	0.09
9RBM1317	13 x 17	20.1	0.79	25.7	1.01	9.5	0.37	11.1	0.44	22.2	0.87	228	9	0.14
9RBM1415	14 x 15	22.0	0.87	23.5	0.92	9.5	0.37	9.5	0.37	19.1	0.75	203	8	0.15
9RBM1617	16 x 17	24.8	0.98	26.2	1.03	9.5	0.37	11.1	0.44	22.2	0.87	229	9	0.18
9RBM1719	17 x 19	26.2	1.03	29.1	1.14	11.1	0.44	11.1	0.44	25.4	1.00	254	10	0.20
9RBM1819	18 x 19	27.7	1.09	29.1	1.14	11.1	0.44	11.1	0.44	25.4	1.00	254	10	0.22
9RBM1922	19 x 22	29.1	1.14	33.4	1.31	11.1	0.44	13.5	0.53	25.4	1.00	254	10	0.25
9RBM1924	19 x 24	28.5	1.12	35.6	1.40	11.1	0.44	14.3	0.56	31.7	1.25	317	12 1/2	0.42
9RBM2022	20 x 22	30.0	1.18	32.9	1.29	12.7	0.50	14.3	0.56	28.6	1.12	279	11	0.33
9RBM2123	21 x 23	31.9	1.26	34.8	1.37	12.7	0.50	14.3	0.56	28.6	1.12	279	11	0.35
9RBM2224	22 x 24	33.4	1.31	36.1	1.42	14.3	0.56	14.3	0.56	31.8	1.25	317	12 1/2	0.46
9RBM2426	24 x 26	35.6	1.40	38.5	1.51	14.3	0.56	15.9	0.63	31.7	1.25	317	12 1/2	0.48
9RBM2427	24 x 27	36.1	1.42	40.4	1.59	15.3	0.60	16.9	0.66	34.9	1.37	356	14	0.59
9RBM2430	24 x 30	35.6	1.40	44.1	1.74	14.3	0.56	15.9	0.63	34.9	1.38	336	14	0.60
2RBM2528	25 x 28	37.7	1.48	40.9	1.61	15.9	0.63	15.9	0.63	34.9	1.38	336	14	0.63
2RBM2730	27 x 30	40.0	1.57	45.0	1.77	16.0	0.63	18.0	0.71	35.0	1.38	356	14	0.68
2RBM2732	27 x 32	41.0	1.61	48.0	1.89	17.0	0.67	18.0	0.71	35.0	1.38	356	14	0.85
2RBM3032	30 x 32	45.5	1.79	47.7	1.88	18.0	0.71	18.0	0.71	35.0	1.38	368	14 1/2	0.77
2RBM3236	32 x 36	47.5	1.87	53.0	2.09	18.0	0.71	20.0	0.79	35.0	1.38	406	16	0.91
2RBM3641	36 x 41	55.5	2.19	61.5	2.42	18.0	0.71	18.0	0.71	43.0	1.69	445	17 1/2	1.81
2RBM4146*	41 x 46	69.5	2.74	75.5	2.97	20.0	0.79	20.0	0.79	47.0	1.85	535	21 3/16	1.96
2RBM4650*	46 x 50	71.0	2.80	77.0	3.03	23.0	0.91	23.0	0.91	50.0	1.97	580	22 13/16	2.30
2RBM5560*	55 x 60	84.0	3.31	92.0	3.62	26.0	1.02	26.0	1.02	56.0	2.20	650	25 5/8	3.00

A/F - Bihexagon

Ref.	A in	D				T				C		L		Wt. kg
		Small end		Large end		Small end		Large end		mm	in	mm	in	
		mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	
2RB2531	1/4 x 5/16	10.7	0.42	13.0	0.51	5.6	0.22	5.6	0.22	11.1	0.44	121	4 3/4	0.03
2RB3137	5/16 x 3/8	13.0	0.51	15.2	0.60	6.4	0.25	6.4	0.25	12.7	0.50	152	6	0.04
2RB3743	3/8 x 7/16	15.2	0.60	17.5	0.69	6.4	0.25	7.1	0.28	12.7	0.50	152	6	0.05
2RB4350	7/16 x 1/2	17.5	0.69	19.7	0.78	7.9	0.31	7.9	0.31	15.9	0.62	178	7	0.09
2RB5056	1/2 x 9/16	19.7	0.78	21.9	0.86	7.9	0.31	9.5	0.37	15.9	0.62	178	7	0.09
2RB5662	9/16 x 5/8	21.9	0.86	24.2	0.95	9.5	0.37	9.5	0.37	19.1	0.75	203	8	0.14
2RB6268	5/8 x 11/16	24.2	0.95	26.4	1.04	9.5	0.37	11.1	0.44	22.2	0.87	229	9	0.19
2RB6875	11/16 x 3/4	26.4	1.04	28.7	1.13	11.1	0.44	11.1	0.44	25.4	1.00	254	10	0.22
2RB7587	3/4 x 7/8	28.7	1.13	33.2	1.31	11.1	0.44	13.5	0.53	25.4	1.00	254	10	0.25
2RB8187	13/16 x 7/8	30.9	1.22	33.2	1.31	12.7	0.50	14.3	0.56	28.6	1.12	279	11	0.33
2RB8793	7/8 x 15/16	32.9	1.30	35.1	1.38	14.3	0.56	14.3	0.56	31.8	1.25	317	12 1/2	0.43
2RB87106	7/8 x 1 1/16	36.5	1.44	41.3	1.63	15.3	0.60	16.9	0.67	34.9	1.38	356	14	0.59
2RB93100	15/16 x 1	35.4	1.39	37.6	1.48	14.3	0.56	15.9	0.62	31.8	1.25	317	12 1/2	0.48
2RB93112	15/16 x 1 1/8	37.7	1.48	40.9	1.61	15.9	0.63	15.9	0.63	34.9	1.38	356	14	0.63
2RB106112	1 1/16 x 1 1/8	40.1	1.58	42.1	1.66	15.9	0.62	15.9	0.62	34.9	1.37	356	14	0.65
2RB106125	1 1/16 x 1 1/4	41.6	1.64	48.6	1.91	17.0	0.67	18.5	0.73	35.0	1.38	381	15	0.77
2RB112131	1 1/8 x 1 5/16	41.6	1.64	48.6	1.91	17.0	0.67	18.5	0.73	35.0	1.38	381	15	0.77
2RB125143	1 1/4 x 1 7/16	46.5	1.83	53.2	2.10	19.1	0.75	20.6	0.81	41.3	1.62	406	16	0.91
2RB131150	1 5/16 x 1 1/2	48.5	1.91	55.6	2.19	18.0	0.71	19.5	0.77	35.0	1.38	394	15 1/2	0.91
2RB143162	1 7/16 x 1 5/8	55.0	2.17	61.0	2.40	18.0	0.71	18.0	0.71	43.0	1.69	450	17 3/4	1.81
2RB162181	1 5/8 x 1 3/16	68.3	2.69	74.4	2.93	20.0	0.79	20.0	0.79	41.0	1.85	530	20 7/8	1.98
2RB168187*	1 11/16 x 1 7/8	69.0	2.72	73.0	2.87	20.0	0.79	20.0	0.79	47.0	1.85	540	21 1/4	1.96
2RB181200*	1 13/16 x 2	71.0	2.80	77.0	3.03	23.0	0.91	23.0	0.91	50.0	1.97	580	22 13/16	2.30

Whitworth - Bihexagon


Ref.	A in	Whit	D		T		C		L		Wt. kg				
			Small end	Large end	Small end	Large end	mm	in	mm	in					
			mm	in	mm	in	mm	in	mm	in					
2RB3344	0.34 x 0.45	1/8 x 3/16	13.9	0.55	17.7	0.70	6.4	0.25	6.4	0.25	12.7	0.50	152	6	0.05
2RB4452	0.45 x 0.53	3/16 x 1/4	17.7	0.70	20.6	0.81	7.9	0.31	7.9	0.31	15.9	0.62	178	7	0.09
2RB5260	0.53 x 0.60	1/4 x 5/16	20.6	0.81	23.3	0.92	9.5	0.37	9.5	0.37	19.1	0.75	203	8	0.18
2RB6071	0.60 x 0.71	5/16 x 3/8	23.3	0.92	27.2	1.07	9.5	0.37	11.1	0.44	22.2	0.87	229	9	0.18
2RB7182	0.71 x 0.82	3/8 x 7/16	27.2	1.07	31.1	1.23	11.1	0.44	11.9	0.47	25.4	1.00	254	10	0.35
2RB8292	0.82 x 0.92	7/16 x 1/2	31.5	1.23	34.7	1.37	12.7	0.50	14.3	0.56	28.6	1.12	279	11	0.33
2RB92101	0.92 x 1.01	1/2 x 9/16	34.7	1.37	38.0	1.49	14.3	0.56	15.9	0.62	31.8	1.25	317	12 1/2	0.48
2RB101110	1.01 x 1.10	9/16 x 5/8	38.0	1.49	41.2	1.62	15.9	0.62	15.9	0.62	34.9	1.37	356	14	0.63
2RB110130	1.10 x 1.30	5/8 x 3/4	41.6	1.64	46.6	1.83	17.0	0.67	18.5	0.67	35.0	1.38	381	15	0.77
2RB120130	1.20 x 1.30	11/16 x 3/4	46.0	1.81	49.2	1.94	18.0	0.71	18.0	0.71	35.0	1.38	369	14 1/2	0.77
2RB130148	1.30 x 1.67	3/4 x 7/8	50.0	1.97	57.0	2.24	18.5	0.73	20.0	0.79	35.0	1.38	406	16	0.91
2RB148167	1.48 x 1.67	7/8 x 1	55.7	2.19	62.7	2.47	18.0	0.71	18.0	0.71	43.0	1.69	483	19	1.81
2RB167186*	1.67 x 1.86	1 x 1 1/8	61.6	2.43	68.4	2.69	20.0	0.79	20.0	0.79	50.8	2.00	535	21	1.96
2RB186205*	1.86 x 2.22	1 1/8 x 1 1/4	71.0	2.80	77.0	3.03	23.0	0.91	23.0	0.91	50.0	1.97	580	22 13/16	2.30

*Shot blast chrome finish.

Britool ring wrenches are double ended and double offset.

Manufactured from the highest quality alloy steel. Bright nickel and chrome plated finish to BS 1224: 1970, service condition No. 1.

All dimensions conform to BS 3555: 1988.



A	Nominal size across flats.
D	Maximum outside diameter of ring.
T	Ring thickness.
C	Crank depth.
G	Gap size.
L	Nominal overall length.