

Interface module - VIP-2/SC/D 9SUB/F/LED - 2322197

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and D-Subminiature socket strip, for mounting on NS 35 rails, with LED, 9-pos.


The illustration shows a 15-position version with a male insert

Why buy this product

- 9 to 50-pos.
- Metal foot
- According to IEC 60603-13
- Screw connection
- 1:1 connection



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 451819
Weight per Piece (excluding packing)	95.3 g
Custom tariff number	85369010
Country of origin	United States

Technical data

Dimensions

Width	34.7 mm
Height	65.5 mm
Depth	45.1 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Interface module - VIP-2/SC/D 9SUB/F/LED - 2322197

Technical data

General

Nominal voltage U_N	24 V DC
Max. current carrying capacity per branch	2.5 A
Number of positions	9
Status display	LED
Mounting position	any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max.	12
Stripping length	8 mm
Screw thread	M3

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB socket strip
Number of positions	9

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

Interface module - VIP-2/SC/D 9SUB/F/LED - 2322197

Classifications

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC001604

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized	
mm ² /AWG/kcmil	30-12
Nominal current I _N	2 A

cUL Recognized	
mm ² /AWG/kcmil	30-12
Nominal current I _N	2 A

Interface module - VIP-2/SC/D 9SUB/F/LED - 2322197

Approvals

cULus Recognized  US

Accessories

Accessories

System cable

Cable - CABLE-D 9SUB/B/S/ 50/KONFEK/S - 2299987



Round shielded cable set, with 9-pos. D-SUB female and male connectors, cable length: 0.5 m

Cable - CABLE-D 9SUB/B/S/100/KONFEK/S - 2299990



Round shielded cable set, with 9-pos. D-SUB female and male connectors, cable length: 1 m

Cable - CABLE-D 9SUB/B/S/150/KONFEK/S - 2300009



Round shielded cable set, with 9-pos. D-SUB female and male connectors, cable length: 1.5 m

Cable - CABLE-D 9SUB/B/S/200/KONFEK/S - 2302010



Round shielded cable set, with 9-pos. D-SUB female and male connectors, cable length: 2 m

Interface module - VIP-2/SC/D 9SUB/F/LED - 2322197

Accessories

Cable - CABLE-D 9SUB/B/S/300/KONFEK/S - 2302023



Round shielded cable set, with 9-pos. D-SUB female and male connectors, cable length: 3 m

Cable - CABLE-D 9SUB/B/S/400/KONFEK/S - 2302036



Round shielded cable set, with 9-pos. D-SUB female and male connectors, cable length: 4 m

Cable - CABLE-D 9SUB/B/S/600/KONFEK/S - 2302049



Round shielded cable set, with 9-pos. D-SUB female and male connectors, cable length: 6 m

Cable - CABLE D-SUB-S/.../.../... - 2302340



Shielded round cable, assembled with one D-SUB male and one female connector, variable cable length

Cable - CABLE D-SUB-S-S/.../.../... - 2302434



Shielded round cable, assembled with two D-SUB male connectors, variable cable length

Drawings

Interface module - VIP-2/SC/D 9SUB/F/LED - 2322197

Circuit diagram

