


METRIC
3rd ANGLE PROJECTION
NUMBER C-174979

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST





注:

- △ $\square$ -Z-面より2mmの範囲で測定
2 適用プリント基板厚:1.6mm
3 嵌合相手ハウジング型番: 174045, 174046
4 推奨取付ネジ: JIS B1115, B1122 タッピンネジ, ナベ2種
呼び径3, 長さ6mm (締付けトルク0.8N-M以下)

NOTE:

- △ TO BE MEASURED WITHIN 2mm FROM $\square$ -Z-
2 APPLICABLE P.C.BOARD THICKNESS: 1.6mm.
3 THE MATING COUNTERPART PART NUMBER: 174045, 174046.
4 RECOMMENDED MOUNTING SCREW: 3mmDIA, 6mmLENGTH
TAPPING SCREW SPECIFIED IN JIS B1115, B1122.
(TIGHTENING TORQUE: 0.8N-M MAX.)

断面 A-A
(SECT. A-A)プリント基板取付穴寸法
(MOUNTING DIMENSIONS FOR P.C. BOARD)
(公差: ± 0.1)
(TOLERANCE: ± 0.1)注, 公差は累積しない事
(NON ACCUMULATE PITCH TOLERANCE)

SELECTIVE-TIN	PRE-TIN	BLACK	2-174979-2
PRE-TIN	PRE-TIN	BLUE	174979-5
PRE-TIN	PRE-TIN	GREEN	174979-4
PRE-TIN	PRE-TIN	BLACK	174979-2
SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上			

Copyright ©1987年
日本電子工業株式会社Copyright ©1987
AMP (Japan) LTD.
ALL RIGHTS RESERVED.tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, Japan

REVISED FJA0-0137-03 TS 4B 29/11/85				材料 (MATERIAL) ハウジング: PBT (HOUSING: PBT) コンタクト: 黄銅 (CONTACT: BRASS)		色 (COLOR) 表参照 (SEE TABLE)		NAME 28極 キャップハウジング アッセンブリ (垂直型) .040シリーズ マルチロック I/O コネクタ (28Pos. CAP HOUSING ASS'Y .040 SERIES MULTI-LOCK I/O CONN. VERTICAL TYPE)			
C	改訂	REVISED	FJ60-0202-89 KI MT 3/12/89	DR. Y. Kakitani 8/3/88		DE. Y. Kakitani 8/3/88		一般公差 (GENERAL TOLERANCES) 0<E 10: ± 0.2 10<E 30: ± 0.25 30<E 100: ± 0.3 ANGLES: $\pm 3^\circ$			
B	追加	2- -2	J-0234 RY AT 7/17/91	DR. Y. Kakitani 8/3/88		DE. Y. Kakitani 8/3/88		SIZE LOC NUMBER B J C-174979			
A	改訂	REVISED	J-12509 Y.K K.Y 5/25/90	DR. Y. Kakitani 8/3/88		DE. Y. Kakitani 8/3/88		SCALE 2-1 REV. D SHEET 1 OF 1			
O	作成	RELEASED	J-10759 Y.K Y.M 8/3/88	CHK. Y. Kakitani 8/3/88		APP. Y. Kakitani 8/3/88					
LTR REVISION RECORD				DR		CHK		DATE			

(CUSTOMER DRAWING) 参考 面