





AMP WIRE RANGE	 Listed
8 AWG SOLID OR STRANDED	8 AWG STRANDED


 LR7189 Certified	MILITARY P/N AND CLASS
8 AWG SOLID OR STRANDED	NOT APPLICABLE

 STAMP AMP 8* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.5MM ² [13,100-20,800] CIR MILS SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	
FOR ORDER ENTRY	1-800-526-5142	

100	LOOSE PIECE, BOX	8-32996-1
1000	ON TAPE, REEL	32996-1
--	LOOSE PIECE	32996
QUANTITY	PACKAGE TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-24-93	 TE Connectivity				
		CHK DA PATTERSON 3-24-93					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DE MILLER 3-24-93	NAME				
	0 PLC ± -	PRODUCT SPEC	TERMINAL, RING TONGUE, SOLISTRAND™				
	1 PLC ± -	—					
	2 PLC ± -	APPLICATION SPEC					
	3 PLC ± -	—					
	4 PLC ± -	—					
MATERIAL	FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
COPPER PER ASTM B-152 ANNEALED	TIN PLATE .00254[0.000100] MIN THICK PER MIL-T-10727	—	A2	00779	C-32996	—	
CUSTOMER DRAWING			SCALE	SHEET	REV		
			8:1	1 of 1	D1		