

General Information

Extended Product Type:	D4/6.4L
Product ID:	1SNA290410R0600
EAN:	3472592904108
Catalog Description:	D4/6.4L Spring Terminal Blocks - Feed-through with 4 connections - Grey
Long Description:	- Easy to access thanks to the front wiring entry, - Clamping contact pressure non dependant on the operator and automatic creeping compensation, - Numerous built-in functions: double jumpering system, clearly visible top marker, test sockets, etc, - Functional through ergonomic design (alignment).

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
CSA Certificate:	1SND162002A0202
Color:	Grey
Connecting Capacity Main Circuit UL/CSA:	Spring Clamp / Flexible 1x 24 ... 10 AWG Spring Clamp / Rigid 1x 24 ... 10 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Connecting Capacity Main Circuit:	Spring Clamp / Flexible 1x 0.2 ... 4 mm ² Spring Clamp / Rigid 1x 0.2 ... 6 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5 ... 4 mm ²
Connection Type:	Spring
Country of Origin:	France (FR)
Customs Tariff Number:	85369010
Data Sheet, Technical Information:	1SNC160019C0202
Declaration of Conformity - CE:	1SND225018U1000
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Dielectric Test Voltage:	3000 V
EAC Certificate:	1SND162001A1100
EAN:	3472592904108
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block
Environmental Information:	1SND220031E1002
Flammability According to UL94:	V0
Function:	Feed-through
Gauge Type:	A4
IT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Instructions and Manuals:	1SNC160019C0202
Insulation Material:	Polyamide
Invoice Description:	D4/6.4L Spring Terminal Blocks - Feed-through with 4 connections - Grey
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Minimum Order Quantity:	50 piece
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Number of Connections:	4
Number of Levels:	1
Object Classification Code:	X
Order Multiple:	50 piece
Package Level 1 EAN:	3472592904108
Package Level 1 Gross Weight:	0.7 kg
Package Level 1 Height:	75 mm
Package Level 1 Length:	200 mm
Package Level 1 Units:	50 piece
Package Level 1 Width:	176 mm
Package Level 2 Gross Weight:	6.200 kg
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Units:	450 piece
Package Level 2 Width:	300 mm
Package Level 3 Units:	21600 piece
Pollution Degree:	3
Product Main Type:	D4/6.4L
Product Name:	Terminal block
Product Net Depth:	37.7 mm
Product Net Height:	37.7 mm
Product Net Length:	37.7 mm
Product Net Weight:	14 g
Product Net Width:	6 mm
Product Packing Type:	Box
RMRS Certificate:	1SND162000A1101
Rated Cross-Section:	4 mm ²
Rated Current (I _n):	Main Circuit 32 A
Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Rated Short-time Withstand Current (I _{cw}):	for 1 s 480 A
Rated Voltage (U _r):	800 V
Recommended Screw Driver:	4 mm
RoHS Information:	1SND230488F0201
Selling Unit of Measure:	piece
Short Description:	Spring Terminal Blocks D4/6.4L
Spacing:	6 mm
Sub-Function:	4 connections
Sub-Function 3:	4 connections
Wire Stripping Length:	11.0 mm
cUL Certificate:	1SND162000A0204
Number of Potentials:	1



