


KEMET Part Number: ALC10A681DH400
(A521EK681M400A)

ALC10, Aluminum Electrolytic, 680 uF, 20%, 400 VDC, -40/+85°C



General Information	
Supplier:	KEMET
Series:	ALC10
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
AEC-Q200:	No
Notes:	Dimensions D And L Include Slewing
Shelf Life:	156 Weeks

Dimensions	
D	35mm +1mm
L	60mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Specifications	
Capacitance:	680 uF
Capacitance Tolerance:	20%
Voltage DC:	400 VDC, 440 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	15000 Hrs (Rated Voltage And Ripple Current At 85C), 24000 Hrs (Rated Voltage at 85C)
Resistance:	232 mOhms (100Hz 20C), 142 mOhms (10kHz 20C)
Ripple Current:	2.9 Amps (100Hz 85C), 4.73 Amps (10kHz 85C)
Leakage Current:	1632 uA (5min 20°C)

Packaging Specifications	
Weight:	80 g
Slewing:	Yes
Packaging:	Bulk, Bag
Packaging Quantity:	100