


## Data Specification Sheet



### EMTWIN65 2 x 3 Watt LED Emergency Non-Maintained Twin Spot

<b>ML Accessories Code</b>	<b>EMTWIN65.</b>
<b>Description</b>	<b>2 X 3W IP65 LED Emergency Twin spot Non-Maintained</b>
<b>Finishes available</b>	White
<b>Overall dimensions (mm) Height – Width - Depth</b>	(H)272mm (W)296mm (D)75mm
<b>Product Weight</b>	1.91kg
<b>Voltage (V)</b>	220-230V 50-60Hz
<b>Lamp Type</b>	2 x 3W Non replaceable LED
<b>Lumen Output</b>	450Lm
<b>Charge Time (Initial)</b>	24 hours
<b>Discharge Duration</b>	3 Hours
<b>Class</b>	Class I. Must be Earthed
<b>IP</b>	IP65
<b>Circuit Power</b>	7 watts
<b>Temperature Range</b>	-10 to +30°C
<b>Battery type</b>	9.6V 2200mah NI-CD Battery
<b>Origin of Manufacture</b>	China
<b>Main materials:</b>	
• <b>Chassis (gear tray)</b>	Powder Coated Pressed Steel
• <b>Body</b>	Self-extinguishing Polycarbonate
• <b>Spot lights</b>	Self-extinguishing Polycarbonate
<b>Method of fix</b>	Direct fixing – Screws provided
<b>Instruction Sheet</b>	Yes
<b>Electrical Connections</b>	Screw terminals
<b>Running Gear</b>	Electronic
<b>F mark</b>	Yes
<b>CE mark</b>	Yes
<b>Quality Assurance System</b>	Yes ISO 9001 QMS
<b>Batch coding details on product</b>	Yes
<b>Certificate of Conformity (Held on File)</b>	Yes
<b>Warranty</b>	2 year
<b>Manufactured in accordance to:</b>	EN55015. EN61547. EN61000-3-2. EN61347-2-7. EN61347-2-3 BSEN60598

ML Accessories Ltd. reserves the right to withdraw, improve or modify any design without prior notification.

ML Accessories Ltd. cannot be held responsible for the incorrect application of any product.