



ECONOMY TRIANGLE mobile flipchart round base

- Lacquered steel board surface
- Magnetic, notes can be stuck to the board with magnets
- Writeable/ dry-wipeable board surface, suitable for writing on with board markers
- Solid round base for stability, including 5 lockable castors
- Robust paper clamp for quick and easy changeover of flipchart paper pads
- Paper hooks are adjustable to suit all major standard paper pad formats
- Pen tray stores a range of markers
- Flipchart board size: H 105 x W 68 cm
- All dark coloured parts and base: Pantone 433C

- 5 year guarantee on the perfect writability and wipeability of the board surface when using Legamaster accessories
- Robust "ruler" paper clamp: tear off paper easily
- Stable round base
- Tool-free mounting system: mounting without additional tools (the round base only needs an open-end wrench for mounting the castors)

Recommended accessories

- STARTER flipchart accessory set
Ref.:7-124900
- TZ41 presentation marker
Ref.:7-155094
- TZ48 presentation marker
Ref.:7-155594

Ref.: **7-153200**

EAN: **8713797084550**





Product specifications

| | |
|----------------------------|------------------------------|
| Marker tray material | ABS |
| Marker tray length | 200 mm |
| Surface (material/colour) | Lacquered steel / - |
| Frame (material/colour) | ABS / - |
| Ergonomic design | No |
| Product dimensions | W: 720 x H: 600 x D: 15 (mm) |
| Total height (min/max) | 1900 / 1900 (mm) |
| Number of castors | 5 |
| Number of lockable castors | 5 |
| Floor space diameter | 635 mm |
| Base | Round |
| Base material | Steel |
| Pad holder | Yes |
| Pad holder material | Plastic |
| Paper blocks | Yes |
| Product warranty | 2 years |
| Surface warranty | 5 years |

Product logistics

| | |
|-------------------------|--------------------------------------|
| Product SAP / EAN / KEA | 867754000 / 8713797084550 / 7-153200 |
| Quantity | 1 |
| Packing dimensions | W: 770 x H: 1140 x D: 135 (mm) |
| Weight (gross/net) | 15.50 kg / 11.99 kg |