




PART NUMBER	DIM "A"
TT121	6 INCHES
TT122	12 INCHES
TT123	18 INCHES
TT124	24 INCHES
TT125	30 INCHES
TT126	3 FEET
TT127	4 FEET
TT128	5 FEET
TT129	6 FEET
TT130	7 FEET
TT131	8 FEET
TT132	9 FEET
TT133	10 FEET
TT134	11 FEET
TT135	12 FEET

PLUG STYLE TT = $\phi 0.173$ CABLE LENGTH (SEE TABLE) CABLE COLOR = GRAY OVERMOLD COLOR = GRAY	TT 121 B 0 CABLE & OVERMOLD COLOR (OPTIONAL) 0 = BLACK 2 = RED 4 = YELLOW 5 = GREEN 6 = BLUE 8 = GRAY** PLUG FINISH (OPTIONAL) B = BRASS N = NICKEL
---	---

** = ONLY SPECIFIED WITH "N" NICKEL PLUG FINISH OPTION

					☆ STAR SYMBOL DENOTES CRITICAL DIMENSION					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
G	23008	10-15-04	DA	TJK	UNLESS OTHERWISE SPECIFIED					SIZE	WIDTH	MULT	LBS/IN	TEMPER		
F	20679	2-6-96	RC	KS	1. ALL DIMENSIONS IN INCHES -TWO PLACE DECIMALS ±0.01 -THREE PLACE DECIMALS ±0.005 -ANGLES ±1° -ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS					FINISH		MATERIAL				
E	20284	10-12-95	DA	TAO						SPEC No.		SPEC No.				
D	19552	7-10-95	ES	TJK						FIRST USED ON		SCALE		Switchcraft®		
C	19703	3-17-95	RC	GHJ						DATE DRWN BY		CHKD	APVD			
B	14602	12-08-88	RLD	JF						10-23-98	FGD	VL	LG	6-2-99		
REV	ECO NUMBER	DATE	BY	APVD	DO NOT SCALE DRAWING					NAME						
REVISIONS					3 CONDUCTOR PATCH CORD					PART No. TT121 - TT130 SERIES TT121B - TT130B SERIES TT121N - TT130N SERIES						
										SHEET 1 OF 1						
										REV G						