

# Housing - HC-B 6-SMLD-52/O1PG16 - 1675269


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Box mounting base, with single locking latch, height 52 mm, without screw connection, 1x Pg16, with protective covers



## Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 150006
Weight per Piece (excluding packing)	236.92 g
Custom tariff number	85389099
Country of origin	Germany

## Technical data

### Dimensions

Height	52 mm
Width	52 mm
Length	84 mm

### Ambient conditions

Degree of protection of housing (IP)	IP65 (When plugged in)
	IP54 (mit geschlossenem Schutzdeckel)
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Note	For contact inserts HC-B6, BB10, DD24, M
Type	B6
Housing type	Box mounting bases
Locking type	With single locking latch
No. of cable outlets	1
Cable exit	Left (view of the opened single locking latch)
Screw connection	none
Type of the screw connection	1x Pg16

# Housing - HC-B 6-SMLD-52/O1PG16 - 1675269

## Technical data

### General

Protective cover	Yes
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA
Material, protective cover	Polyamide
Assembly instructions	For half and full screw connections

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC

---

# Housing - HC-B 6-SMLD-52/O1PG16 - 1675269

## Approvals

Ex Approvals

---

Approvals submitted


---

Approval details

EAC
-----

## Drawings

Dimensional drawing



Dimensional drawing; h = 52 mm, a = 40 mm, b = 52 mm