







10 9 8 7 6 5 4 3 2 1




ISOMETRIC VIEW

NOTES.


1. MATERIAL : $\textcircled{P}$ BRASS, PRE-TIN PLATED
2. FINISH : 0.8~1.8 μ m,Tin(Sn) plating overall
0.3~0.8 μ m,Copper(Cu) plating
3. PRODUCT SPECIFICATION : PS-35150-001, PS-35180-002
PS-35180-003, PS-35524-001
4. CRIMPING SPECIFICAITON : CS-35745-001
5. RECOMMENDED LENGTH OF WIRE STRIP IS 4.0~4.8mm




SEC' : X-X''



SEC' : Y-Y''



SEC' : W-W''



MATERIAL NO	ENG. No.	AWG	a	b	c	d	PITCH 'P'
357450210	35745-0210	#18-#14	3.4	3.8	5.2	4.8	12.0
357450110	35745-0110	#22-#20	2.85	2.8	4.2	4.0	10.6
357450410	35745-0410	#24	2.2	1.75	3.85	3.5	10.6

REVISED
EC NO: KOR2009-0151
TDRWN: JHPARK01 2009/05/18
CHKD: WY. YANG 2009/06/18
APPR: YUNSIKKIM 2009/07/01

QUALITY
SYMBOLS
=0
=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± 0.2	± ---
1 PLACE	± 0.3	± ---

ANGULAR ± 1 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE
JS.KANG	1998/01/19
CHECKED BY	DATE
BK.CHOI	1998/01/19
APPROVED BY	DATE
CW.LEE	1998/01/19

MATERIAL NO.

SEE TABLE

SCALE
4:1

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
.070 MALE TERMINAL
(A-TYPE)

MOLEX INCORPORATED

DOCUMENT NO.
SD-35745-001

SHEET NO.
1 OF 01

9 8 7 6 5 4 3 2 1