

Disconnect terminal block - PT 2,5-TWIN-TGB - 3210193

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Disconnect terminal block, Connection type: Push-in connection, Cross section: 0.14 mm² - 4 mm², AWG: 26 - 12, Nominal current: 16 A, Nominal voltage: 400 V, Length: 81.9 mm, Width: 5.2 mm, Color: gray, Assembly: NS 35/7,5, NS 35/15

Product Features

- ✓ The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- ✓ The compact design and front connection enable wiring in a confined space
- ✓ In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection
- ✓ Tested for railway applications



Key commercial data

| | |
|------------------------|----------|
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Custom tariff number | 85369010 |
| Country of origin | Poland |

Technical data

General

| | |
|---|--|
| Note | The max. load current must not be exceeded by the total current of all connected conductors. Current and voltage are determined by the plug used. |
| Number of levels | 1 |
| Number of connections | 3 |
| Color | gray |
| Insulating material | PA |
| Inflammability class according to UL 94 | V0 |
| Area of application | Railway industry |
| | Mechanical engineering |
| | Plant engineering |

Disconnect terminal block - PT 2,5-TWIN-TGB - 3210193

Technical data

General

| | |
|---|--|
| Rated surge voltage | 6 kV |
| Pollution degree | 3 |
| Surge voltage category | III |
| Insulating material group | I |
| Connection in acc. with standard | IEC 60947-7-1 |
| Maximum load current (lower level) | 16 A |
| Additional text | with 4 mm ² conductor cross section |
| Nominal current I _N (lower level) | 16 A |
| Nominal voltage U _N | 400 V |
| Open side panel | ja |
| Shock protection test specification | DIN EN 50274 (VDE 0660-514):2002-11 |
| Back of the hand protection | guaranteed |
| Finger protection | guaranteed |
| Surge voltage test setpoint | 7.3 kV |
| Result of surge voltage test | Test passed |
| Power frequency withstand voltage setpoint | 1.89 kV |
| Result of power-frequency withstand voltage test | Test passed |
| Checking the mechanical stability of terminal points (5 x conductor connection) | Test passed |
| Bending test rotation speed | 10 rpm |
| Bending test turns | 135 |
| Bending test conductor cross section/weight | 0.14 mm ² / 0.2 kg |
| | 2.5 mm ² / 0.7 kg |
| | 4 mm ² / 0.9 kg |
| Result of bending test | Test passed |
| Conductor cross section tensile test | 0.14 mm ² |
| Tractive force setpoint | 10 N |
| Conductor cross section tensile test | 2.5 mm ² |
| Tractive force setpoint | 50 N |
| Conductor cross section tensile test | 4 mm ² |
| Tractive force setpoint | 60 N |
| Tensile test result | Test passed |
| Tight fit on carrier | NS 35 |
| Setpoint | 1 N |
| Result of tight fit test | Test passed |
| Result of voltage drop test | Test passed |
| Temperature-rise test | Test passed |

Disconnect terminal block - PT 2,5-TWIN-TGB - 3210193

Technical data

General

| | |
|---|--|
| Conductor cross section short circuit testing | 2.5 mm ² |
| Short-time current | 0.3 kA |
| Short circuit stability result | Test passed |
| Ageing test for screwless modular terminal block temperature cycles | 192 |
| Result of aging test | Test passed |
| Proof of thermal characteristics (needle flame) effective duration | 30 s |
| Result of thermal test | Test passed |
| Test specification, oscillation, broadband noise | DIN EN 50155 (VDE 0115-200):2008-03 |
| Test spectrum | Service life test category 2, bogie mounted |
| Test frequency | f ₁ = 5 Hz to f ₂ = 250 Hz |
| ASD level | 6.12 (m/s ²) ² /Hz |
| Acceleration | 3.12g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Oscillation, broadband noise test result | Test passed |
| Test specification, shock test | DIN EN 50155 (VDE 0115-200):2008-03 |
| Shock form | Half-sine |
| Acceleration | 30g |
| Shock duration | 18 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Shock test result | Test passed |
| Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Static insulating material application in cold | -60 °C |

Dimensions

| | |
|------------------|----------|
| Width | 5.2 mm |
| Length | 81.9 mm |
| Height | 35.20 mm |
| Height NS 35/7,5 | 36.7 mm |
| Height NS 35/15 | 44.2 mm |

Connection data

| | |
|--|----------------------|
| Connection in acc. with standard | IEC 60947-7-1 |
| Connection method | Push-in connection |
| Conductor cross section solid min. | 0.14 mm ² |
| Conductor cross section solid max. | 4 mm ² |
| Conductor cross section AWG/kcmil min. | 26 |

Disconnect terminal block - PT 2,5-TWIN-TGB - 3210193

Technical data

Connection data

| | |
|---|----------------------|
| Conductor cross section AWG/kcmil max | 12 |
| Conductor cross section stranded min. | 0.14 mm ² |
| Conductor cross section stranded max. | 2.5 mm ² |
| Min. AWG conductor cross section, stranded | 26 |
| Max. AWG conductor cross section, stranded | 14 |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.14 mm ² |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 2.5 mm ² |
| Conductor cross section stranded, with ferrule with plastic sleeve min. | 0.14 mm ² |
| Conductor cross section stranded, with ferrule with plastic sleeve max. | 2.5 mm ² |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 0.5 mm ² |
| Minimum stripping length | 8 mm |
| Maximum stripping length | 10 mm |
| Internal cylindrical gage | A3 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141126 |
| eCl@ss 4.1 | 27141126 |
| eCl@ss 5.0 | 27141126 |
| eCl@ss 5.1 | 27141120 |
| eCl@ss 6.0 | 27141120 |
| eCl@ss 7.0 | 27141120 |
| eCl@ss 8.0 | 27141126 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000902 |
| ETIM 4.0 | EC000902 |
| ETIM 5.0 | EC000902 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Disconnect terminal block - PT 2,5-TWIN-TGB - 3210193

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / GOST / VDE Zeichengenehmigung / IEC/IEE CB Scheme / CSA / GL / BV / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized

| | | B | C | D |
|--------------------------------|-------|-------|-------|---|
| mm ² /AWG/kcmil | 26-12 | 26-12 | 26-12 | |
| Nominal current I _N | 16 A | 16 A | 5 A | |
| Nominal voltage U _N | 300 V | 300 V | 600 V | |

cUL Recognized

| | | B | C | D |
|--------------------------------|-------|-------|-------|---|
| mm ² /AWG/kcmil | 26-12 | 26-12 | 26-12 | |
| Nominal current I _N | 16 A | 16 A | 5 A | |
| Nominal voltage U _N | 300 V | 300 V | 600 V | |

GOST

VDE Zeichengenehmigung

| | |
|----------------------------|---------|
| mm ² /AWG/kcmil | 0.2-2.5 |
|----------------------------|---------|

Disconnect terminal block - PT 2,5-TWIN-TGB - 3210193

Approvals

| | |
|--------------------|-------|
| | |
| Nominal current IN | 16 A |
| Nominal voltage UN | 400 V |

| | |
|----------------------------|-------|
| IECEE CB Scheme | |
| | |
| mm ² /AWG/kcmil | 2.5 |
| Nominal current IN | 16 A |
| Nominal voltage UN | 400 V |

| | | | |
|----------------------------|-------|-------|-------|
| CSA | | | |
| | B | C | D |
| mm ² /AWG/kcmil | 26-12 | 26-12 | 26-12 |
| Nominal current IN | 16 A | 16 A | 5 A |
| Nominal voltage UN | 300 V | 300 V | 600 V |

| |
|----|
| GL |
|----|

| |
|----|
| BV |
|----|

| |
|------------------|
| cULus Recognized |
|------------------|

Drawings

Circuit diagram

