

# Housing - HC-B 6-SML-52/O1PG16 - 1675214

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Box mounting base, with single locking latch, height 52 mm, without screw connection, 1x Pg16

Figure shows product with height of 74 mm



## Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 149970
Weight per Piece (excluding packing)	202.9 g
Custom tariff number	85389099
Country of origin	Germany

## Technical data

### Dimensions

Height	52 mm
Width	52 mm
Length	84 mm

### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

### General

Note	For contact inserts HC-B6, BB10, DD24, M
Type	B6
Housing type	Box mounting bases
Locking type	With single locking latch
No. of cable outlets	1
Cable exit	Left (view of the opened single locking latch)
Screw connection	none

# Housing - HC-B 6-SML-52/O1PG16 - 1675214

## Technical data

### General

Type of the screw connection	1x Pg16
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

# Housing - HC-B 6-SML-52/O1PG16 - 1675214

## Approvals

Approvals submitted


---

## Approval details


EAC
-----

## Drawings

Schematic diagram



Dimensional drawing



Dimensional drawing; h = 52 mm, a = 40 mm, b = 52 mm