

CoreLine Panel

RC125B LED34S/840 PSU W60L60

RC125B - LED Module, system flux 3400 lm - Power supply unit

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

• General information

Product family code	RC125B [RC125B]
Lamp family code	LED34S [LED Module, system flux 3400 lm]
Lamp colour code	840 [840 white]
Light source replaceable	No [No]
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes [Yes]
Luminaire light beam spread	110 [110 degrees]
Dimmable	No [No]
Connection	PIP [Push-in connector and pull relief]
Protection class IEC	CLII [Safety class II]
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Colour	WH [White]
Flammability mark	F [For mounting on normally flammable surfaces]
Safety device	SC [Safety cable]
CE mark	CE [CE mark]
ENEC mark	No [-]
UL mark	No [-]

• Light technical

Luminous flux tolerance	5%
-------------------------	----

• Electrical

Input voltage	220-240 V [220 to 240 V]
Input frequency	50-60 Hz [50 to 60 Hz]

• Mechanical

Geometry	W60L60 [Width 0.60 m, length 0.60 m]
Housing material	STL [Steel]
Optic material	PMMA [Polymethyl methacrylate]

• Initial perform. (IEC compliant)

Initial input power	41 W [41 W]
Initial luminous flux	3400 Lm
Initial LED luminaire efficacy	83 Lm/W
Lamp colour temperature	4000 [4000 K]
Colour Rendering Index	>80 [>80]
Initial chromaticity	(0.38, 0.38) SDCM <5

• Over time perform. (IEC compliant)

Median useful life	30000 hr
L80B50	
Driver failure rate at 5000 h	1.5 %

• Application conditions

Average ambient temperature	T25 [+25 °C]
Ambient temperature range	+10 to +40°C [+10 to +40 °C]
Suitable for random switching	Yes [Yes (relates to presence/movement detection and daylight harvesting)]



PHILIPS

CoreLine Panel


Product Data

Order code 067314 00
 Full product code 871869606731400
 Full product name RC125B LED34S/840 PSU W60L60
 Order product name RC125B LED34S/840 PSU W60L60
 Pieces per pack 0
 Packs per outerbox 1
 Bar code on 8718696067314
 outerbox - EAN3

Logistic code(s) - 910503910025
 12NC
 Net weight per piece 4.500 kg




Dimensional drawing



RC125B LED34S/840 PSU W60L60

Photometric data



RC125B W60L60 1xLED34S/840



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of
Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, August 5
data subject to change