

## General Information

<b>Extended Product Type:</b>	S201-C63
<b>Product ID:</b>	2CDS251001R0634
<b>EAN:</b>	4016779551014
<b>Catalog Description:</b>	Miniature Circuit Breaker - S200 - 1P - C - 63 ampere
<b>Long Description:</b>	System pro M compact S200 miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 6 kA at 230/400 V AC) and rated currents (up to 63A). All MCBs of the product range S200 comply with IEC/EN 60898-1, IEC/EN 60947-2, UL1077 and CSA 22.2 No. 235, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200 to save 50% space.

## Ordering

<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85362010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	2CDC002157D0102
<b>Instructions and Manuals:</b>	2CSC400002D0208

## Dimensions

<b>Product Net Width:</b>	17.5 mm
<b>Product Net Depth / Length:</b>	69 mm
<b>Product Net Height:</b>	88 mm
<b>Product Net Weight:</b>	0.125 kg

## Technical

<b>Standards:</b>	IEC/EN 60898-1 IEC/EN 60947-2 UL 1077
<b>Number of Poles:</b>	1
<b>Tripping Characteristic:</b>	C
<b>Rated Current (I<sub>n</sub>):</b>	63 A
<b>Rated Operational Voltage:</b>	acc. to IEC 60898-1 230 / 400 V AC acc. to IEC 60947-2 230 V AC

<b>Power Loss:</b>	4.8 W at Rated Operating Conditions per Pole 4.8 W
<b>Rated Insulation Voltage (U<sub>i</sub>):</b>	acc. to IEC/EN 60664-1 440 V
<b>Operational Voltage:</b>	Maximum (Incl. Tolerance) 253 V AC Maximum (Incl. Tolerance) 72 V DC Maximum 253 V AC Maximum 72 V DC Minimum 12 V AC Minimum 12 V DC
<b>Rated Frequency (f):</b>	50 Hz 60 Hz
<b>Rated Short-Circuit Capacity (I<sub>cn</sub>):</b>	(230 / 400 V AC) 6 kA
<b>Rated Ultimate Short-Circuit Breaking Capacity (I<sub>cu</sub>):</b>	(133 V AC) 20 kA (230 V AC) 10 kA
<b>Rated Service Short-Circuit Breaking Capacity (I<sub>cs</sub>):</b>	(133 V AC) 15 kA
<b>Energy Limiting Class:</b>	3
<b>Overvoltage Category:</b>	III
<b>Pollution Degree:</b>	3
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	4 kV (6.2 kV @ sea level) (5.0 kV @ 2000 m)
<b>Dielectric Test Voltage:</b>	50 / 60 Hz, 1 min: 2 kV
<b>Housing Material:</b>	Insulation Group II, RAL 7035
<b>Actuator Type:</b>	Insulation group II, black, sealable
<b>Contact Position Indication:</b>	Red ON / Green OFF
<b>Degree of Protection:</b>	IP20
<b>Remarks:</b>	IP40 in enclosure with cover
<b>Electrical Endurance:</b>	10000 AC cycle
<b>Mechanical Endurance (N<sub>endu</sub>):</b>	20000 cycle
<b>Terminal Type:</b>	Screw Terminals
<b>Screw Terminal Type:</b>	Failsafe Bi-directional Cylinder-lift Terminal
<b>Connecting Capacity:</b>	Busbar 10 / 10 mm <sup>2</sup> Flexible with Ferrule 0.75 ... 25 mm <sup>2</sup> Flexible 0.75 ... 25 mm <sup>2</sup> Rigid 0.75 ... 35 mm <sup>2</sup> Stranded 0.75 ... 35 mm <sup>2</sup>
<b>Tightening Torque:</b>	2.8 N·m
<b>Recommended Screw Driver:</b>	Pozidriv 2
<b>Mounting on DIN Rail:</b>	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
<b>Mounting Position:</b>	Any

## Environmental

<b>Ambient Air Temperature:</b>	Operation -25 ... +55 °C Storage -40 ... +70 °C
<b>Resistance to Shock acc. to IEC 60068-2-27:</b>	25g / 2 shocks / 13 ms
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
<b>Environmental Conditions:</b>	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	60 V DC 480Y/277 V AC
<b>Connecting Capacity UL/CSA:</b>	Busbar 18-8 AWG Conductor 18-4 AWG
<b>Tightening Torque UL/CSA:</b>	25 in·lb
<b>Interrupting Rating acc. to UL1077:</b>	(133 V AC) 6 kA (277 V AC) 6 kA (480Y / 277 V AC) 6 kA (60 V DC) 10 kA

## Certificates and Declarations (Document Number)

<b>Declaration of Conformity - CE:</b>	2CDK403001D0604
<b>Environmental Information:</b>	2CDK400030D0201
<b>Instructions and Manuals:</b>	2CSC400002D0208
<b>RoHS Information:</b>	2CDK400003K0201

## Container Information

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	92 mm
<b>Package Level 1 Depth / Length:</b>	183 mm
<b>Package Level 1 Height:</b>	80 mm
<b>Package Level 1 Gross Weight:</b>	1.295 kg
<b>Package Level 1 EAN:</b>	4016779607360
<b>Package Level 2 Units:</b>	120 piece
<b>Package Level 2 Width:</b>	275 mm
<b>Package Level 2 Depth / Length:</b>	395 mm
<b>Package Level 2 Height:</b>	210 mm
<b>Package Level 2 Gross Weight:</b>	14.8 kg

Package Level 2 EAN: 4016779971256

## Classifications

**Object Classification Code:** F

**E-nummer:** 2100532

**ETIM 4:** EC000042 - Miniature circuit breaker (MCB)

**ETIM 5:** EC000042 - Miniature circuit breaker (MCB)

**ETIM 6:** EC000042 - Miniature circuit breaker (MCB)

**ETIM 7:** EC000042 - Miniature circuit breaker (MCB)

**eClass:** 7.0 27141901

**UNSPSC:** 39121614

## Accessories

Identifier	Description	Type	Qty	Unit Of Measure
2CCA880100R0001	Strom-Messsystem Sensor CMS-100PS 80A, 18mm für pro M compact u. SMISLINE	CMS-100PS	1	piece
2CCA880101R0001	Strom-Messsystem Sensor CMS-101PS 40A, 18mm für pro M compact u. SMISLINE	CMS-101PS	1	piece
2CCA880102R0001	Strom-Messsystem Sensor CMS-102PS 20A, 18mm für pro M compact u. SMISLINE	CMS-102PS	1	piece
2CDS200909R0001	S2C-A1 - Arbeitsstromauslöser	S2C-A1	1	piece
2CDS200909R0002	S2C-A2 - Arbeitsstromauslöser	S2C-A2	1	piece
2CDS200912R0001	S2C-H6R - Hilfskontakt	S2C-H6R	1	piece
2CDS200918R0001	S2C-NT - Manueller Neutralleiter	S2C-NT	1	piece
2CDS200922R0001	S2C-S/H6R - Signalkontakt / Hilfsschalter	S2C-S/H6R	1	piece
2CDS200936R0001	S2C-H11L - Hilfskontakt	S2C-H11L	1	piece
2CDS200936R0002	S2C-H20L - Hilfskontakt	S2C-H20L	1	piece
2CDS200936R0003	S2C-H02L - Hilfskontakt	S2C-H02L	1	piece
2CDS200946R0001	S2C-H6-11R - Hilfsschalter	S2C-H6-11R	1	piece
2CDS200946R0002	S2C-H6-20R - Hilfskontakt	S2C-H6-20R	1	piece

<b>Identifizier</b>	<b>Description</b>	<b>Type</b>	<b>Qty</b>	<b>Unit Of Measure</b>
2CDS200946R0003	S2C-H6-02R - Hilfskontakt	S2C-H6-02R	1	piece
2CDS200970R0001	S2C-H01 - Hilfskontakt	S2C-H01	1	piece
2CDS200970R0002	S2C-H10 - Hilfskontakt	S2C-H10	1	piece
2CSS200911R0001	S2C-UA 12 DC - Unterspannungsauslöser	S2C-UA 12 DC	1	piece
2CSS200911R0002	S2C-UA 24 AC - Unterspannungsauslöser	S2C-UA 24 AC	1	piece
2CSS200911R0003	S2C-UA 48 AC - Unterspannungsauslöser	S2C-UA 48 AC	1	piece
2CSS200911R0004	S2C-UA 110 AC - Unterspannungsauslöser	S2C-UA 110 AC	1	piece
2CSS200911R0005	S2C-UA 230 AC - Unterspannungsauslöser	S2C-UA 230 AC	1	piece
2CSS200911R0006	S2C-UA 400 AC - Unterspannungsauslöser	S2C-UA 400 AC	1	piece
2CSS200911R0007	S2C-UA 24 DC - Unterspannungsauslöser	S2C-UA 24 DC	1	piece
2CSS200911R0008	S2C-UA 48 DC - Unterspannungsauslöser	S2C-UA 48 DC	1	piece
2CSS200911R0009	S2C-UA 110 DC - Unterspannungsauslöser	S2C-UA 110 DC	1	piece
2CSS200911R0010	S2C-UA 230 DC - Unterspannungsauslöser	S2C-UA 230 DC	1	piece
2CSS200998R0001	S2C-BP - Mechanischer Auslöser	S2C-BP	1	piece
2CSS200999R0001	S2C-EST - Stecksockel	S2C-EST	1	piece
2CSS201997R0013	S2C-CM1 - Motorantrieb	S2C-CM1	1	piece
2CSS203997R0013	S2C-CM2/3 - Motorantrieb	S2C-CM2/3	1	piece
2CSS204997R0013	S2C-CM4 - Motorantrieb	S2C-CM4	1	piece
GHS2001901R0003	S2C-DH - Antrieb	S2C-DH	1	piece

