




Technical drawing of a PCB layout for a 14-pin D-sub connector. The drawing shows a rectangular board with dimensions 35,56 mm (width) and 2,54 mm (height). A central 14-pin connector footprint is defined by a dashed rectangle. The footprint has a width of 17,78 mm (7 x 2,54 mm) and a height of 2,54 mm. The footprint is divided into two rows of 7 pins each, labeled "1st contact" and "2nd contact". The distance between the two rows is 1,52 mm. The distance from the left edge of the board to the left edge of the footprint is 2,54 mm. The distance from the right edge of the footprint to the right edge of the board is 2,54 mm. The distance from the top edge of the board to the top edge of the footprint is 2,54 mm. The distance from the bottom edge of the footprint to the bottom edge of the board is 2,54 mm. The footprint has a central hole with a diameter of 0,05 mm, labeled "All holes 1". The footprint has a minimum diameter of 2,8 mm, labeled "Min. ø 2,8". The footprint has a diameter of 0,05 mm, labeled "ø 0,05".

09 18 516 7909	3
09 18 516 6909	2
09 18 516 5909	1 (0,76 $\mu\text{m Au}$)
Part number	Performance level

				Dat.	Name		SEK 18 Male Connector Standard 16 poles Press in Long locking levers	Maßstab/ Scale 1,5:1
			Detail.	11/09/06	PK			
			Insp.					
EC00823	16/09/09	PK	Stand.					
33950	13/03/07	PK	HARTING EURL F-95972 Paris				TB 09 18 516 X909	Blatt/ Page 1 / 1
33803	11/09/06	PK						
Mod.	Dat.	Name					Sub.	