



# Turning - Toolholders, internal

## Toolholders for inserts DCMT and DCMW



• Inserts, please see pages 112, 149, 164



Application		Part No.	Dimensions in mm							∅ min		KG	
			d	h	b	l <sub>1</sub>	f <sub>1</sub>	l <sub>3</sub>	a <sub>r</sub>				
107°30' 	07	S10L-SDQCR07-R	10	-	-	140	7	25	1,5	13	0,1	DCM.0702..	
		S12N-SDQCR07-R	12	-	-	160	9	30	2,5	17	0,1	DCM.0702..	
		S16Q-SDQCR07	16	15	15,5	180	11	40	2,5	22	0,2	DCM.0702..	
		S10L-SDQCL07-R	10	-	-	140	7	25	1,5	13	0,1	DCM.0702..	
		S12N-SDQCL07-R	12	-	-	160	9	30	2,5	17	0,1	DCM.0702..	
		S16Q-SDQCL07-R	16	-	-	180	11	40	2,5	22	0,3	DCM.0702..	
	11	S20R-SDQCR11	20	18	19	200	13	50	2,5	25	0,4	DCM.11T3..	
		S20R-SDQCL11-R	20	-	-	200	13	50	2,5	25	0,5	DCM.11T3..	
	15	S25S-SDQCR15	25	23	24	250	17	50	4	32	0,8	DCM.1504..	
		S25S-SDQCL15-R	25	-	-	250	17	50	4	32	0,9	DCM.1504..	

## Spare Parts, Parts included in delivery

Toolholder/ Insert dimension	Locking screw/ Key	
...07/R	C02506	T07-2
...11/R	C04008	T15-2
...15/R	C04512	T15-2

Please check availability in current price and stock-list