

Product datasheet

Characteristics

14879

DuoLine XP - comb busbar cut - 1P - type N - 18 mm pitch - 13 modules - 63A



Main

Range	DuoLine
Product or component type	Comb busbar
Device short name	Bar'clic XP
Accessory / separate part category	Connection accessory
Poles description	1P
Number of ways	13 ways, type : N (tooth) with 18 mm pitch
Distance between way	18 mm
Total number of 18 mm modules	13

Complementary

Insulation	Insulated
Device presentation	Cutable
[Ie] rated operational current	63 A (40 °C)
[Ue] rated operational voltage	230 V AC Ph/N
[Ui] rated insulation voltage	250 V AC
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	26
Width	234 mm
Colour	Blue
Range compatibility	DuoLine / DuoLine D'clic XP DuoLine / DuoLine D'clic Vigi DuoLine / DuoLine ID'clic XP

Environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0849 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.