

## General Information

|                               |  |
|-------------------------------|--|
| <b>Extended Product Type:</b> | BJMI5-3  |
| <b>Product ID:</b>            | 1SNA176279R1700  |
| <b>EAN:</b>                   | 3472591762792  |
| <b>Catalog Description:</b>   | BJMI5-3 POLES Jumper Bars  |
| <b>Long Description:</b>      | - IP20 assembled screw jumper bars, - Fractionnable model with captive screws and spacer s, - Allows connection between consecutive blocks only. |

## Additional Information

|   |  |
|---|--|
| <b>ABB Industrial IT Suite:</b>           | Control IT   |
| <b>Ambient Air Temperature:</b>           | Operation -55 ... +110 °C  |
| <b>Color:</b>                             | Grey   |
| <b>Country of Origin:</b>                 | France (FR)  |
| <b>Customs Tariff Number:</b>             | 85369010   |
| <b>Data Sheet, Technical Information:</b> | 1SNC160001C0207-CH-J Accessories   |
| <b>Declaration of Conformity - CE:</b>    | 1SND225001C1009  |
| <b>Degree of Protection:</b>              | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20   |
| <b>EAN:</b>                               | 3472591762792  |
| <b>ETIM 4:</b>                            | EC000489 - Cross-connector for terminal block  |
| <b>ETIM 5:</b>                            | EC000489 - Cross-connector for terminal block  |
| <b>ETIM 6:</b>                            | EC000489 - Cross-connector for terminal block  |
| <b>Function:</b>                          | Jumper Bars  |
| <b>IIT Publishing Status:</b>             | Level 0 - Information enabled  |
| <b>Industrial IT Certification Level:</b> | 0  |
| <b>Instructions and Manuals:</b>          | 1SNC160001C0207-CH-J Accessories   |
| <b>Insulation Material:</b>               | Polyamide  |
| <b>Invoice Description:</b>               | BJMI5-3 POLES Jumper Bars  |
| <b>Minimum Order Quantity:</b>            | 10 piece   |
| <b>Mounting Type:</b>                     | Fractionnable model, composed of captive screws on a jumper bar, with IP20 protection touchproof. This accessory can be used for connecting consecutive blocks only. |
| <b>Mounting on DIN Rail:</b>              | G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715<br>TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715<br>TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715   |
| <b>Object Classification Code:</b>        | X  |
| <b>Order Multiple:</b>                    | 10 piece   |
| <b>Package Level 1 EAN:</b>               | 3472591762792  |
| <b>Package Level 1 Gross Weight:</b>      | 0.05 kg  |
| <b>Package Level 1 Height:</b>            | 5 mm   |
| <b>Package Level 1 Length:</b>            | 200 mm   |
| <b>Package Level 1 Units:</b>             | 10 piece   |
| <b>Package Level 1 Width:</b>             | 155 mm   |
| <b>Package Level 2 Units:</b>             | 500 piece  |
| <b>Package Level 3 Units:</b>             | 90000 piece  |
| <b>Product Main Type:</b>                 | BJMI   |
| <b>Product Name:</b>                      | Jumper Bar   |
| <b>Product Net Depth:</b>                 | 5 mm   |
| <b>Product Net Height:</b>                | 20.6 mm  |

|                                       |  |
|---------------------------------------|--|
| <b>Product Net Weight:</b>            | 5 g  |
| <b>Product Net Width:</b>             | 5 mm   |
| <b>Product Packing Type:</b>          | Bag  |
| <b>Rated Current (I<sub>n</sub>):</b> | Main Circuit 24 A  |
| <b>RoHS Information:</b>              | 1SND230492F0201  |
| <b>Selling Unit of Measure:</b>       | piece  |
| <b>Spacing:</b>                       | 5 mm   |
| <b>Sub-Function:</b>                  | Assembled jumper bar   |
| <b>Sub-Function 2:</b>                | Screw  |
| <b>Suitable For:</b>                  | D1.5/5.ADO.NF<br>D1/5.ADO<br>D1/5.D2.ADO<br>D2.5/5.ADO<br>D2.5/5.D2.ADO<br>MA2.5/5<br>MA2.5/5-2CPE<br>MA2.5/5-CPE<br>MA2.5/5D-2CPE |

