

# Specifications for BMP71 Label Printer Labels

|                                 |  |
|---------------------------------|--|
| <b>Adhesive</b>                 | Permanent Acrylic - Foam Backed  |
| <b>Article No.</b>              | 622219   |
| <b>Brady Material No.</b>       | <a href="#">B-7593</a>   |
| <b>Material Type</b>            | Polyethylene-foam Laminate Polyester   |
| <b>Colour</b>                   | White  |
| <b>Finish</b>                   | Gloss  |
| <b>Order Reference</b>          | M71EP-1-7593-WT  |
| <b>Printer Compatibility</b>    | BMP71  |
| <b>Size - Height (mm)</b>       | 8.00   |
| <b>Size - Width (mm)</b>        | 27.00  |
| <b>Thickness (mm)</b>           | 0.65   |
| <b>Total Qty per Pack</b>       | 250 Label(s) / Box   |
| <b>Vertical Repeat (mm)</b>     | 11.18  |
| <b>Ribbon Series</b>            | M71-R6000HF  |
| <b>Application</b>              | Electrical Component Marking   |
| <b>Industry</b>                 | Data & Telecommunications;Electrical;Facility & Safety Identification;General Industry;Manufacturing;Process   |
| <b>Layout</b>                   | Roll Mounted   |
| <b>Description</b>              | Thermal transfer printable raised panel labels. Designed to make legend plate creation quick, less expensive, and hassle free! Use for electrical components, electrical cabinets, push buttons, patch panels, and any other applications you can imagine. This material can also be used for rating and serial plates using alphanumeric that require name plate quality. |
| <b>Max. Characters per Line</b> | 22   |
| <b>Max. Lines of Text</b>       | 3  |
| <b>Max. Service Temp. °C</b>    | 100  |
| <b>Min. Service Temp. °C</b>    | -40  |
|                                 |  |

