

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1707290005](#)
Status: **Active**
Overview: iPass+™ HD Interconnect System
Description: iPass+™ zHD Vertical Single Piece Housing Assembly, 0.76µm

Documents:

[3D Model](#) [Product Specification PS-170729-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E107635

General

Product Family I/O Connectors
 Series [170729](#)
 Application Wire-to-Board
 Component Type Internal Receptacles
 Overview [iPass+™ HD Interconnect System](#)
 Product Name iPass+™, zHD™
 Type N/A
 UPC 887191414942

Physical

Circuits (Loaded) 36
 Circuits (maximum) 36
 Color - Resin Black
 Durability (mating cycles max) 50
 Flammability 94V-0
 Lock to Mating Part Yes
 Material - Metal Copper Alloy
 Material - Plating Mating Gold over Nickel
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 3.798/g
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 1.57mm
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 1.57mm
 Packaging Type Tray
 Panel Mount No
 Pitch - Mating Interface 0.75mm
 Plating min - Mating 0.076µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Temperature Range - Operating -40°C to +80°C
 Termination Interface: Style Through Hole - Compliant Pin
 Waterproof / Dustproof No

Electrical

Current - Maximum per Contact 1.0A
 Voltage - Maximum 48V DC

Solder Process Data

Lead-freeProcess Capability N/A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2015 June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

[170729](#) Series

Mates With

[111074](#) iPass Internal Cable Assembly

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
I-PASS™ zHD Vertical Housing Assembly Removal Tool	0622024800
I-PASS™ zHD Wafer Assembly Removal Tool	0622024900

Material Info

Reference - Drawing Numbers

Electrical Model Document

EE-170729-0001

Product Specification

PS-170729-001

S-Parameter Model

SP-170729-0001

Sales Drawing

SD-170729-0005

This document was generated on 08/18/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION