

22MM PLASTIC ROUND COMPLETE UNIT
COMBINATION: PUSHBUTTON WITH RAISED BUTTON
SCREW TERMINAL,
1NO+1NC WITH HOLDER WHITE

Actuator / signaling device:		
Design of the operating mechanism		Pushbutton
Type of unlocking device		without
Color / of the activation element		Green
Material / of the activation element		plastic
Shape / of the activation element		Raised pushbutton
Number of switching positions		2
Product component / front ring		Yes
Material / of the front ring		plastic
Color / of the front ring		black
Design of front ring		Standard
Product function / EMERGENCY STOP function		No

Contact block / lampholder		
Design of the electrical connection		screw-type terminals
Number of switching elements		1
Number of NC contacts / for auxiliary contacts		1
Number of NO contacts / for auxiliary contacts		1
Number of change-over switches / for auxiliary contacts		0
Product function / positive opening		Yes
Number of lampholders		0
Product component / fluorescent materials		No
Product extension / optional / fluorescent materials		No

Accessories:		
Product component / holder for 3 switching elements		No

General technical details:		
Type of voltage / of the operating voltage		AC/DC
Operating voltage / rated value		
• minimum	V	5
• maximum	V	400

Operating current		
<ul style="list-style-type: none"> • at AC-12 <ul style="list-style-type: none"> • at 24 V / rated value • at 48 V / rated value • at 110 V / rated value • at 230 V / rated value • at 400 V / rated value • at AC-15 <ul style="list-style-type: none"> • at 24 V / rated value • at 48 V / rated value • at 110 V / rated value • at 230 V / rated value • at 400 V / rated value • at DC-12 <ul style="list-style-type: none"> • at 24 V / rated value • at 48 V / rated value • at 110 V / rated value • at 230 V / rated value • at DC-13 <ul style="list-style-type: none"> • at 24 V / rated value • at 48 V / rated value • at 110 V / rated value • at 230 V / rated value 	A	10
	A	10
	A	10
	A	10
	A	10
	A	6
	A	6
	A	6
	A	6
	A	3
	A	10
	A	5
	A	2.5
	A	1
	A	3
	A	1.5
	A	0.7
	A	0.3
Resistance against shock		
<ul style="list-style-type: none"> • for devices without incandescent lamp / according to IEC 60068-2-27 		<= 50g
Resistance against vibration / according to IEC 60068-2-6		20 ... 200 Hz: 5g
Operating cycles / maximum	1/h	1,000
Mechanical operating cycles as operating time / typical		10,000,000
Item designation		
<ul style="list-style-type: none"> • according to DIN EN 61346-2 • according to DIN 40719 extendable after IEC 204-2 / according to IEC 750 		S
		S
Tightening torque / of the screws in the bracket / maximum	N·m	1
Ambient temperature		
<ul style="list-style-type: none"> • during operating • during storage 	°C	-25 ... +70
	°C	-40 ... +80
Protection class IP		IP66
climatic class / during the operating phase / according to EN 60721		3K6
Type of mounting		front mounting

Shape / of the installation hole		round
Installation width	mm	29.5
Mounting diameter	mm	22
Mounting height	mm	12
Mounting depth	mm	63

Certificates/approvals:

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



[Special Test Certificate](#)

Shipping Approval



other

[Confirmation](#)

[other](#)



Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SB3201-0BA61/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3201-0BA61

last change:

Jul 17, 2012