

LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					N2	REVISED PER ECO-11-004587	11MAR11	RK	HMR

D

D

C





C

B



B

A

A



RECOMMENDED HOLE PATTERN



BASIC DIMENSIONS FOR ODD NO OF SPACES (SEE TABLE)

BASIC DIMENSIONS FOR EVEN NO OF SPACES (SEE TABLE)

- 1 CONTACT AREAS PLATED WITH .000030 GOLD, SOLDER TAILS PLATED WITH .000150 TIN-LEAD, ALL OVER .000050 NICKEL
- 2 POINT OF MEASUREMENT FOR GOLD THICKNESS
- 3 CIRCUIT IDENTIFICATION FEATURE OMITTED ON 4,5,6 AND 7 POSITION HEADER ASSEMBLIES
- 4 DIMENSION APPLIES AT BASE OF SHROUD
- 5 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST & HOUSING
- 6 Y 3, Y 4 ARE LOCATED THE SAME AS Y 1, Y 2 EXCEPT ON OPPOSITE SIDE OF HOUSING
- 7 CONTACT AREAS PLATED WITH .000030 GOLD, SOLDER TAILS PLATED WITH .000150 TIN, ALL OVER .000050 NICKEL
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1	OBSELETE	1.250	25	1.430	26	7-104071-0
2	OBSELETE	2.450	49	2.630	50	6-104071-9
3	OBSELETE	2.200	44	2.380	45	6-104071-8
4	OBSELETE	1.950	39	2.130	40	6-104071-7
5	OBSELETE	1.750	35	1.930	36	6-104071-6
6	OBSELETE	1.300	26	1.480	27	6-104071-5
7	OBSELETE	1.050	21	1.230	22	6-104071-4
8	OBSELETE	.800	16	.980	17	6-104071-3
9	OBSELETE	.600	12	.780	13	6-104071-2
10	OBSELETE	.550	11	.730	12	6-104071-1
11	OBSELETE	.350	7	.530	8	6-104071-0
12	OBSELETE	.300	6	.480	7	5-104071-9
13	OBSELETE	.250	5	.430	6	5-104071-8
14	OBSELETE	.150	3	.330	4	5-104071-7
15	OBSELETE	1.450	29	1.630	30	5-104071-6
16	OBSELETE	1.200	24	1.380	25	5-104071-5
17	OBSELETE	.950	19	1.130	20	5-104071-4
18	OBSELETE	.700	14	.880	15	5-104071-3
19	OBSELETE	.200	4	.380	5	5-104071-2
20	OBSELETE	.450	9	.630	10	5-104071-1
21	OBSELETE	1.250	25	1.430	26	2-104071-0
22	OBSELETE	2.450	49	2.630	50	1-104071-9
23	OBSELETE	2.200	44	2.380	45	1-104071-8
24	OBSELETE	1.950	39	2.130	40	1-104071-7
25	OBSELETE	1.750	35	1.930	36	1-104071-6
26	OBSELETE	1.300	26	1.480	27	1-104071-5
27	OBSELETE	1.050	21	1.230	22	1-104071-4
28	OBSELETE	.800	16	.980	17	1-104071-3
29	OBSELETE	.600	12	.780	13	1-104071-2
30	OBSELETE	.550	11	.730	12	1-104071-1
31	OBSELETE	.350	7	.530	8	1-104071-0
32	OBSELETE	.300	6	.480	7	104071-9
33	OBSELETE	.250	5	.430	6	104071-8
34	OBSELETE	.150	3	.330	4	104071-7
35	OBSELETE	1.450	29	1.630	30	104071-6
36	OBSELETE	1.200	24	1.380	25	104071-5
37	OBSELETE	.950	19	1.130	20	104071-4
38	OBSELETE	.700	14	.880	15	104071-3
39	OBSELETE	.200	4	.380	5	104071-2
40	OBSELETE	.450	9	.630	10	104071-1
		C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. HELM 12-19-88	TE Connectivity			
DIMENSIONS: INCHES		CHK H. MOLL 12-19-88	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. DURBIN 12-19-88	PRODUCT SPEC			
0. PLC ± .005		1. PLC ± .005	APPLICATION SPEC			
2. PLC ± .005		3. PLC ± .005	114-25031			
4. PLC ± .005		ANGLES ± .005	100779C=104071			
MATERIAL HOUSING: THERMOPLASTIC COLOR: BLACK CONTACT: COPPER ALLOY		FINISH 1 2	CUSTOMER DRAWING			
		SCALE 4:1	SHEET 1 of 1		REV N2	