

Crimping pliers - CRIMPFOX 6-M - 1212720


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6.0 mm², lateral entry, trapezoidal crimp

Product Features

- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross sections
- Consistently high crimping quality
- Unlockable pressure lock
- Marked die stations for precise processing of corresponding cross sections



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	600.0 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	204 mm
Width (a)	22 mm
Height	76 mm

General

Color	black
Compression	Trapezoidal crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1

Crimping pliers - CRIMPFOX 6-M - 1212720

Technical data

General

Min. cross section	0.25 mm ²
Max. cross section	0.75 mm ²
AWG min	24
AWG max	20
Designation	Crimping position 2
Min. cross section	1 mm ²
Max. cross section	1.5 mm ²
AWG min	18
AWG max	16
Designation	Crimping position 3
Max. cross section	2.5 mm ²
AWG max	14
Die station	Crimping position 4
Max. cross section	4 mm ²
AWG max	12
Die station	Crimping position 5
Max. cross section	6 mm ²
AWG max	10

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21049090
eCl@ss 9.0	21049090

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
-------------	----------

Crimping pliers - CRIMPFOX 6-M - 1212720

Classifications

UNSPSC

UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518