







SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	15	NO MISSING SYMBOL NUMBER	
	LAST NO. USED	13		

DWG STATUS				REVISION HISTORY				AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG	ZONE					1	2
15FE06	R	B2	-	-		CLEARED REV COLUMN, UPDATED TO LATEST U8 STANDARD. MAT'L SPEC WAS R0071754 AND ADDED NOTES 6 & 7				277186	JTZ FRG B06
13SE06	R	B3	-	-		UPDATED PDM ATTRIBUTES				284433	MM MM B06
05DE06	R	B4	-	-		REVISED MODEL TO MATCH PART				287497	RH RH B06



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MAXIMUN CABLE DIAMETER FOR THIS PART IS 2.8 MM.
 - SEALING CODE 3 - DESIGN WILL PASS SALT FOG AND IMMERSION TEST AFTER CONDITIONING AS SPECIFIED IN ESA-644 (WEATHER-PACK), ESA-710 (METRI-PACK), ESA-650 (UNDERHOOD MICRO-PACK), C-4006 (WORLD CONNECTOR), ETC. - WHEN MATED TO MATING PART OR EQUIVALENT
 - THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
 - THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT: CONNECTOR TO MATE WITH 12110293 CONNECTOR AND SEAL ASSEMBLY CAVITIES TO ACCEPT 12045773 TERMINAL SECONDARY TERMINAL LOCK 12052845 CABLE SEAL 12048086 CONNECTOR POSITION ASSURANCE T-LOCK 12020833 WHEN MATED WITH 12110293 CONNECTOR AND SEAL ASM
 - MATERIAL RECYCLING CODE PER ISO 11469. (1.5)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
 - (0.9)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".

DIMENSIONAL RANGE (MM)		SHORT		ET	
FROM	> 0	> 30	> 70	> 100	> 150
TO	20	30	70	100	150
TOLERANCE UNLESS OTHERWISE SPECIFIED					
[0.15] ±0.2 [0.3] ±0.4 [0.5] ±0.6 [0.8] ±1 [1.2] ±1.2					
ANGULAR TOLERANCE 22°					

PROCESS SENSITIVE DIMENSION	PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED

THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA
------------------------	--------------	---------------

ALL DIMENSIONS ARE IN MILLIMETERS	REFERENCE
12052844	12052844

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS WARREN, OH	
DR	DATE
APVD1 W. H. POEHLER	13FE92
APVD2 HENRY HOKE	13FE92
APVD3 W. K. CHIN	13FE92
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
WATERBURY W3592001 PA66 HS 1M BLK	
DRAWING NAME	
CONN 3 M M/P 150 BLK SLD	
DRAWING NUMBER	
12129615	
SIZE A0	SCALE 5:1
FRAME NO 1	SHEET NO 1 OF 1
STG REV R B4	N/P