

D09S13A4GX00LF - D-Subminiature Delta
D : Signal 9 way Socket Right Angle Solder
Europe standard, 200 cycles, Harpoons +
Threaded Insert UNC 4 - 40 + Elec cont., 1.6
mm PCB thickness



www.fci.com

Mating Half

DE09P064TXLF

865609PLTXLF

Specifications

Approvals / Certifications	
Approvals / Certifications	Recognized File E 118235 (R)
Mechanical	
Durability (Plating - Mating cycles)	Std Class (>200 Mating Cycles)
Extraction force (Mating part)	0.3N min. Per contact
Insertion force (Mating part)	5N max. Per contact
Dimensional	
Size (Shell)	E
Thickness (Board)	1.6 mm
Electrical	
Current rating	5A Per contact
Resistance (Contact)	< 10 milli-ohms
Voltage rating	300V rms at 50 Hz
Voltage rating (DWV - Dielectric withstanding)	1000V rms
General	
Contact type	Signal
Gender	Socket
Number of contacts (Total)	9
Orientation	Right Angle
Product Type	Connector
Termination Style	Solder
Mounting	
Attachment	Board
Mounting accessory	Harpoons + Threaded Insert UNC 4-40 + Electrical continuity
Termination	Europe standard
Other Features	
Most Popular Configuration	Yes
Physical	
Plating (Contact)	

	Gold over Nickel
Plating (Shell)	Bright Pure Tin over Nickel
Plating (Termination)	Matte Tin over Nickel
Temperature (Operating - range)	-55°C to +125°C