




LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P3	REVISED PER ECO-11-004587	11MAR11	RK	HMR

- 1 HOUSING: FLAME RETARDANT, THERMOPLASTIC, BLACK
POST: BRASS
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 THE NOTED DIMENSIONS APPLY FROM THE BASIC
DIMENSION LINE (NOT THE POST CENTERLINE)
TO THE SURFACE INDICATED
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS,
TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS,
ONE POLARIZATION SLOT.
- 5 FOR USE WITH .062±008 PRINTED CIRCUIT BOARD
- 6 .000030 GOLD IN THE CONTACT AREA,
.000100—.000200 MATTE TIN—LEAD ON THE
SOLDER TAIL, ALL OVER .000050 NICKEL
- 7 .000030 GOLD IN THE CONTACT AREA,
.000100—.000200 MATTE TIN ON THE
SOLDER TAIL, ALL OVER .000050 NICKEL
- 8 HIGH TEMPERATURE CONFIGURATION.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

OBSOLETE 9	8	7	2.600	2.520	2.400	24	25	7-103904-4		
			2.500	2.420	2.300	23	24	7-103904-3		
			2.400	2.320	2.200	22	23	7-103904-2		
			2.300	2.220	2.100	21	22	7-103904-1		
OBSOLETE 9			2.200	2.120	2.000	20	21	7-103904-0		
			2.100	2.020	1.900	19	20	6-103904-9		
			2.000	1.920	1.800	18	19	6-103904-8		
			1.900	1.820	1.700	17	18	6-103904-7		
OBSOLETE 9			1.800	1.720	1.600	16	17	6-103904-6		
			1.700	1.620	1.500	15	16	6-103904-5		
			1.600	1.520	1.400	14	15	6-103904-4		
			1.500	1.420	1.300	13	14	6-103904-3		
OBSOLETE 9			1.400	1.320	1.200	12	13	6-103904-2		
			1.300	1.220	1.100	11	12	6-103904-1		
			1.200	1.120	1.000	10	11	6-103904-0		
			1.100	1.020	.900	9	10	5-103904-9		
OBSOLETE 9			1.000	.920	.800	8	9	5-103904-8		
			.900	.820	.700	7	8	5-103904-7		
			.800	.720	.600	6	7	5-103904-6		
			.700	.620	.500	5	6	5-103904-5		
OBSOLETE 9			.600	.520	.400	4	5	5-103904-4		
			.500	.420	.300	3	4	5-103904-3		
			.400	.320	.200	2	3	5-103904-2		
			.300	.220	.100	1	2	5-103904-1		
OBSOLETE 9			6	6	2.600	2.520	2.400	24	25	2-103904-4
OBSOLETE 9					2.500	2.420	2.300	23	24	2-103904-3
OBSOLETE 9					2.400	2.320	2.200	22	23	2-103904-2
OBSOLETE 9					2.300	2.220	2.100	21	22	2-103904-1
OBSOLETE 9					2.200	2.120	2.000	20	21	2-103904-0
OBSOLETE 9					2.100	2.020	1.900	19	20	1-103904-9
OBSOLETE 9					2.000	1.920	1.800	18	19	1-103904-8
OBSOLETE 9					1.900	1.820	1.700	17	18	1-103904-7
OBSOLETE 9					1.800	1.720	1.600	16	17	1-103904-6
OBSOLETE 9					1.700	1.620	1.500	15	16	1-103904-5
OBSOLETE 9					1.600	1.520	1.400	14	15	1-103904-4
OBSOLETE 9					1.500	1.420	1.300	13	14	1-103904-3
OBSOLETE 9					1.400	1.320	1.200	12	13	1-103904-2
OBSOLETE 9					1.300	1.220	1.100	11	12	1-103904-1
OBSOLETE 9					1.200	1.120	1.000	10	11	1-103904-0
OBSOLETE 9					1.100	1.020	.900	9	10	103904-9
OBSOLETE 9					1.000	.920	.800	8	9	103904-8
OBSOLETE 9					.900	.820	.700	7	8	103904-7
OBSOLETE 9					.800	.720	.600	6	7	103904-6
OBSOLETE 9					.700	.620	.500	5	6	103904-5
OBSOLETE 9					.600	.520	.400	4	5	103904-4
OBSOLETE 9					.500	.420	.300	3	4	103904-3
OBSOLETE 9					.400	.320	.200	2	3	103904-2
OBSOLETE 9					.300	.220	.100	1	2	103904-1
6-103904-2	REMARKS	PLATING			D	C	B	A	NO OF POS	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIM 5-17-93 E. BRANDBERG CHK 5-17-93 J. GESFORD		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± . 1 PLC ± . 2 PLC ± . 3 PLC ± .005 4 PLC ± . ANGLES ± .		NAME HEADER ASSY, AMPMODU MTE, RIGHT ANGLE, SINGLE ROW, 100CL .025 SQ POSTS, WITH LATCH & HOLD DOWNS	
		APVD — PRODUCT SPEC 108-25034 APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO A1 00779	
MATERIAL 		FINISH SEE TABLE		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 OF 1 REV P3	