

**G12S2  
Angle Grinder**



Excellent overload durability  
Coated coil armature gives superior resistance to dust abrasion  
High efficiency cooling fan  
Torsion spring brush retention ensures maximum brush life  
Compact body length (only 250mm)  
Reduced body diameter (only 62mm)

Wheel diameter	115mm (4.5")
Arbor	22mm
Spindle Thread	M14 x 2
Power Input	800W (230V) 760W (110V)
No-load Speed	11000/min
Overall Length	250mm
Weight	1.6kg
Standard Accessories	Abrasive wheel Wrench Side handle