



Part Number: 9533

RS-232, #24-3c, SR-PVC, O/A Foil, PVC Jkt, CMG

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, PVC insulation, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
24	7x32	TC - Tinned Copper	3

Total Number of Conductors:	3
-----------------------------	---

Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.011 in

Color Chart

Number	Color
1	Black
2	White
3	Red

Outer Shield Material

Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.162 in	0.032 in

Electrical Characteristics

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
33 pF/ft	65 pF/ft

Construction and Dimensions

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
25 Ohm/1000ft	18 Ohm/1000ft

Current

Max. Recommended Current [A]
1.75 Amps per conductor @ 25°C A

Voltage

UL Voltage Rating

300V RMS

Applicable Standards & Environmental Programs

CEC/C(UL) Specification:	CMG
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CPR Euroclass:	Eca
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Standards

NEC/(UL) Specification:	CMG
UL AWM Style:	2464 (300 V 80°C)

Flame Test

CSA Flammability:	FT4
UL Flammability:	UL1685 FT4 Loading

Safety

UL Voltage Rating:	300 V RMS
--------------------	-----------

Mechanical Characteristics

Operating Temp Range:	-30°C To +80°C
Bulk Cable Weight:	16(lbs/1000ft)
Max Recommended Pulling Tension:	16.5(lbs)
Min Bend Radius/Minor Axis:	1.75(in)

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2464)
-----------------	--------------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

History

Variants

Item #	Color
9533.0030	Chrome
9533.00U152	Chrome
9533.00U305	Chrome
9533.01152	Chrome
9533.01305	Chrome
9533 060100	Chrome
9533 0601000	Chrome
9533 060500	Chrome
9533 0605000	Chrome
9533 060U1000	Chrome
9533 060U500	Chrome

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.