



## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LX1D2
Control circuit type	AC 50 Hz
[Uc] control circuit voltage	110 V AC 50 Hz
Average resistance	148.2 Ohm at 20 °C
Inductance of closed circuit	5.7 H
Product compatibility	LC1D09...D18

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.8...1.1 Uc at ≤ 55 °C operational 50 Hz
Inrush power in VA	60 VA at 20 °C (cos f 0.75) 50 Hz
Hold-in power consumption in VA	7 VA at 20 °C (cos f 0.3) 50 Hz

## Environment

Product weight	0.7 kg
----------------	--------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0702 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product environmental</a>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

Product end of life instructions

Available

 [End of life manual](#)

---