

KEMET Part Number: C1210C226Z9VACTU
(C1210C226Z9VAC7800)

Capacitor, Ceramic, SMD, MLCC, General Purpose, Class III, 22 uF, -20/+80% Tol, 6.3 V, Y5V, 1210 (3225 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1210 (3225 metric)
Temperature Coefficient:	Y5V
Part Type Description:	SMD, MLCC, General Purpose, Class III
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	2.5	+/-0.2
T	1.9	+/-0.20
B	0.5	+/-0.25

Specifications	
Capacitance:	22 uF
Voltage:	6.3 V
Tolerance:	-20/+80%
Temperature Range:	-30/+85C
Dissipation Factor:	10%
Failure Rate:	N/A
Aging Rate:	7% loss/decade hour
Insulation Resistance:	2 MOhm
Dielectric Strength:	15.75 V
Miscellaneous:	Note: Referee time for Y5V dielectric for this part number is 48 hours

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2000