


## MKDS 3/ 4

Order No.: 1711042



PC terminal block, Nominal current: 24 A, Nom. voltage: 400 V, Pitch: 5 mm, Number of positions: 4, Connection method: Screw connection, Mounting: Soldering, Conductor/PCB connection direction: 0 °, Color: green, The article can be aligned to create different nos. of positions!

| Commercial data          |   |
|--------------------------|---|
| EAN                      | 4  017918 023676 |
| Pack                     | 50  |
| Customs tariff           | 85369010  |
| Country of Origin        | DE  |
| Catalog page information | Page 97 (CC-2011)   |

### Product notes

WEEE/RoHS-compliant since: 01/01/2003



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

| Technical data                |         |
|-------------------------------|---------|
| <b>Dimensions / positions</b> |         |
| Length                        | 11.2 mm |
| Height                        | 18 mm   |
| Pitch                         | 5 mm    |
| Dimension a                   | 15 mm   |

|                        |              |
|------------------------|--------------|
| Number of positions    | 4            |
| Pin dimensions         | 0,9 x 0,9 mm |
| Pin spacing            | 5 mm         |
| Hole diameter          | 1.3 mm       |
| Screw thread           | M3           |
| Tightening torque, min | 0.5 Nm       |
| Tightening torque max  | 0.6 Nm       |

#### Technical data

|   |   |
|---|---|
| Range of articles                       | MKDS 3  |
| Insulating material group               | I   |
| Rated surge voltage (III/3)             | 4 kV  |
| Rated surge voltage (III/2)             | 4 kV  |
| Rated surge voltage (II/2)              | 4 kV  |
| Rated voltage (III/3)                   | 250 V   |
| Rated voltage (III/2)                   | 400 V   |
| Rated voltage (II/2)                    | 630 V   |
| Connection in acc. with standard        | EN-VDE  |
| Nominal current $I_N$                   | 24 A  |
| Nominal cross section                   | 2.5 mm <sup>2</sup>                                   |
| Maximum load current                    | 28 A (with 4 mm <sup>2</sup> conductor cross section) |
| Insulating material                     | PA  |
| Inflammability class according to UL 94 | V0  |
| Internal cylindrical gage               | A3  |
| Stripping length                        | 8 mm  |
| Nominal voltage, UL/CUL Use Group B     | 300 V   |
| Nominal current, UL/CUL Use Group B     | 15 A  |
| Nominal voltage, UL/CUL Use Group D     | 300 V   |
| Nominal current, UL/CUL Use Group D     | 10 A  |

#### Connection data

|  |                      |
|--|----------------------|
| Conductor cross section solid min.   | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.   | 4 mm <sup>2</sup>    |
| Conductor cross section stranded min.                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section stranded max.                                      | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |

|   |                      |
|---|----------------------|
| Conductor cross section stranded, with ferrule without plastic sleeve max.              | 2.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.                 | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.                 | 2.5 mm <sup>2</sup>  |
| Conductor cross section AWG/kcmil min.  | 24                   |
| Conductor cross section AWG/kcmil max   | 12                   |
| 2 conductors with same cross section, solid min.  | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, solid max.  | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded min.                                     | 0.2 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded max.                                     | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.25 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 0.75 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 1.5 mm <sup>2</sup>  |
| Minimum AWG according to UL/CUL   | 30                   |
| Maximum AWG according to UL/CUL   | 12                   |

## Certificates



Certification

CCA, CSA, CUL, GL, GOST, SEV, UL

## Accessories

| Item | Designation | Description |
|------|-------------|-------------|
|------|-------------|-------------|

### Assembly

|         |                |   |
|---------|----------------|---|
| 1703047 | RZ 1,25-MKDS 3 | Pitch spacer, for adjusting the pitches between MKDS and GMKDS terminal blocks in mixed rows, 1.25 mm thick |
|---------|----------------|---|

---

**Bridges**

|         |          |   |
|---------|----------|---|
| 1733172 | EBP 3- 5 | Insertion bridge, fully insulated, for plug connectors with 5.0 or 5.08 mm pitch, no. of positions: 3 |
| 1733185 | EBP 4- 5 | Insertion bridge, fully insulated, for plug connectors with 5.0 or 5.08 mm pitch, no. of positions: 4 |

**General**

|         |          |   |
|---------|----------|---|
| 1733169 | EBP 2- 5 | Insertion bridge, fully insulated, for plug connectors with 5.0 or 5.08 mm pitch, no. of positions: 2 |
|---------|----------|---|

**Marking**

|         |                        |  |
|---------|------------------------|--|
| 1051993 | B-STIFT                | Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm  |
| 0804183 | SK 5/3,8:FORTL.ZAHLEN  | Marker card, printed horizontally, self-adhesive, 12 identical decades marked 1-10, 11-20 etc. up to 91-(99)100, sufficient for 120 terminal blocks  |
| 0805072 | SK 5/3,8:SO            | Marker card, special printing, self-adhesive, labeled acc. to customer requirements, 12 identical marker strips per card, max. 25-position labeling per strip, color: white                          |
| 0805409 | SK 5/3,8:UNBEDRUCKT    | Marker cards, unprinted, with pitch division marks, self-adhesive, 10-pos. marker strips, 12 strips per card, can be labeled with B-STIFT  |
| 0803906 | SK U/3,8 WH:UNBEDRUCKT | Unprinted marker cards, DIN A4 format, pitch as desired, self-adhesive, with 40 stamped marker strips, 185 mm strip length, can be labeled with the CMS system or manually with the B-STIFT or X-PEN |

**Tools**

|         |             |  |
|---------|-------------|--|
| 1205053 | SZS 0,6X3,5 | Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip |
|---------|-------------|--|


---

---

## Drawings

Drilling plan/solder pad geometry

---



Dimensioned drawing

---

