


NO	DESCRIPTION	DATE
⚠	UFL PLUG — SMT PLUG JPC UFL PLUG — PBT.G.G	09.28.10'



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-3 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 WORKING VOLTAGE: 100 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 200 VOLTS
- 1.5 VSWR: 1.5 MAX.

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
PHOSPHOR BRONZE
- 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B106 UNS C17300
PHOSPHOR BRONZE
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
PBT(DURANEX 3128),UL94V-0

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -40° C TO +90° C

4	SMT CONNECTOR	1	PBT.G.G	⚠
3	CABLE	1	ø1.13	
2	HEAT SHRINK TUBE	1	BLACK	
1	19-04-8 1.13 (50Ω)	1	T.G.G	
NO	DESCRIPTION	Q'TY	FINISH	



APPROVED

by _____ DATE: _____

DESCRIPTION		SMA BULKHEAD REAR MOUNT JACK CRIMP ST. + SMT PLUG WHIT Ø1.13 CABLE	
製圖	DRAWN Yoko	TOLERANCE .X ±0.2	品名 YH43-77
檢圖	CHECK Arc	.XX ±0.1	TITLE ROHS COMPLIANT
修正	APPROVAL Jenny	.XXX ±0.05	DATE 04.19.10'
	ANGLE ±5°	單位 mm(In)	圖次 A-1
		比例 4:1	DWG.NO. 99-0395
		SCALE	