

4


3

2




1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	-	A5		REVISED PER ECO-11-005030	26APR11	RK HMR



1. 材料:ハウジング:ガラス入り熱可塑性ポリエステル樹脂(94V-0)、色:黒
コンタクト:銅合金
リテンションレグ:錫めっき済銅合金
2. めっき:全面:ニッケル下地めっき1.27μm以上
3. めっき:接触部 2 の上に金めっき0.38μm以上
4. めっき:コンタクト半田付部: 2 の上に錫めっき2μm以上
5. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。
6. Y KEY形状は、X KEY形状と左右対称




推奨基板取付穴寸法:コネクタ搭載面(非累積公差)
PC基板厚:1.0~1.6±0.1
RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1





1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER(94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY

2. FINISH(ALL OVER): NICKEL PL. 1.27μmMIN
3. FINISH(CONTACT AREA): GOLD PL. 0.38μmMIN AFTER 2
4. FINISH(CONTACT TAIL): TIN PL. 2μmMIN AFTER 2
5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
6. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

20	Y	9	22.5	26.0	27.6	2-1827875-0
20	X	9	22.5	26.0	27.6	1-1827875-0
16	Y	7	17.5	21.0	22.6	2-1827875-8
16	X	7	17.5	21.0	22.6	1-1827875-8
12	Y	5	12.5	16.0	17.6	2-1827875-6
12	X	5	12.5	16.0	17.6	1-1827875-6
10	Y	4	10.0	13.5	15.1	2-1827875-5
10	X	4	10.0	13.5	15.1	1-1827875-5
8	Y	3	7.5	11.0	12.6	2-1827875-4
8	X	3	7.5	11.0	12.6	1-1827875-4
6	Y	2	5.0	8.5	10.1	2-1827875-3
6	X	2	5.0	8.5	10.1	1-1827875-3
4	Y	1	2.5	6.0	7.6	2-1827875-2
4	X	1	2.5	6.0	7.6	1-1827875-2
POS	KEY	n	A	B	C	PART NO



DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5° 0-PLC ± 1-PLC ±0.5 2-PLC ±0.13 3-PLC ±0.013 4-PLC ±0.0001 ANGLES ± MATERIAL 材料		DWN T.KUDO 14JAN2005		 TE Connectivity	
				CHK D.MITSUGI 14JAN2005			
				APVD D.MITSUGI 14JAN2005		NAME 名称 DYNAMIC DI200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS	
				PRODUCT SPEC 製品規格 108-78268			
				APPLICATION SPEC 取付適用規格 114-5377			
				WEIGHT -			
CUSTOMER DRAWING		SCALE 尺度 4:1		SHEET 1 OF 3		REV A5	

4

4POS(X-KEY):1-1827875-2


3

2

1





THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
J	-			SEE SHEET 1		






推奨基板取付穴寸法: コネクタ搭載面 (非累積公差)
PC基板厚: 1.0~1.6±0.1
RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

ONLY 4POS






SCALE 2:1

4POS(X-KEY):1-1827875-2



6POS(X-KEY):1-1827875-3



8POS(X-KEY):1-1827875-4

DIMENSIONS:		DWN	T. KUDO	14JAN2005	 TE Connectivity	
		CHK	D. MITSUGI	14JAN2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D. MITSUGI	14JAN2005	NAME	
		PRODUCT SPEC	108-78268			
MATERIAL		APPLICATION SPEC	114-5377		DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) 4-20POS	
		WEIGHT	-			
FINISH		SIZE	A3	00779	CAGE CODE	C-1827875
		CUSTOMER DRAWING	SCALE	4:1	SHEET	2 OF 3
0. PLC ± 1. PLC ± 2. PLC ± 3. PLC ± 4. PLC ± ANGLES ±		RESTRICTED TO	REV		A5	

