

Belden Wire & Cable - Paired Cable

Mid-High Capacitance Computer Cable

Overall Beldfoil® Shield

24 AWG, 15 Pairs

For EIA RS-232 Applications

Trade Number: 9515

NEC CMG  
UL AWM 2464  
CSA AWM  
CEC CMG

Conductor AWG: 24  
Conductor Stranding: (7x32)  
Conductor Type: TC  
Conductor DCR: 24 ohms/M'

Insulation Type: S-R PVC

Jacket Type: PVC

Shield Type: Beldfoil

Nominal OD: 0.413 in.

Nominal Capacitance: 30 pF/ft\*

Nominal Capacitance: 50 pF/ft\*\*

Velocity of Prop.: 60%

**Standard Lengths(ft.) Standard Units(lbs.)**

100	10.4
500	53
1000	102.3

<b>Frequency(Mhz)</b>	<b>Max. Atten(dB/M')</b>	<b>Min. NEXT(dB)</b>
-----------------------	--------------------------	----------------------

**DESCRIPTION**

Tinned copper, S-R PVC insulated, twisted pairs. Overall Beldfoil® aluminum-polyester shield. 24 AWG stranded tinned copper drain wire. Chrome PVC jacket. 100% shield coverage.

Rating: 300V 80°C

\*Capacitance between conductors.

\*\*Capacitance between one conductor and other conductors connected to shield.