

RefLED ES50

RefLED ES50 V2 DIM 345LM 830 36° SL

0026592



Range features

PRODUCT OVERVIEW

Ordering number	26592
Technology	LED
Light colour	830 Warm White
Energy class	A+
Average life (Rated) (h)	15000
Lamp shape	Reflector
Lamp finish	White
Dimmable	Yes
Cap/Base	GU10
Type	RefLED ES50
CRI (Ra)	80
Beam angle(°)	36
Colour temperature (K)	3000
Useful luminous flux (Rated) (lm)	345
Efficacy (Rated) (lm/w)	58
Watt (Nominal) (W)	6.0
Equivalent watt (W)	50
Voltage (V)	220-240

RefLED ES50

RefLED ES50 V2 DIM 345LM 830 36° SL

0026592

DATA TABLE

General data

Ordering number	26592
Technology	LED
Energy class	A+
Average life (Rated) (h)	15000
Energy saving lamp	Yes
Average life (Nominal) (h)	15000
Lamp shape	Reflector
Lamp finish	White
Dimmable	Yes
Cap/Base	GU10
Type	RefLED ES50
Product name	RefLED ES50 V2 DIM 345LM 830 36° SL
Starting time (max) (s)	<0,5
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	20000
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

Optical data

Light colour	830 Warm White
CRI (Ra)	80
Beam angle (Rated) (°)	36
Suitable for accent lighting	Yes
Beam angle(°)	36
Colour Consistency	6
Colour temperature (K)	3000
Lumen maintenance at end of nominal life (%)	85
Useful luminous flux (Rated) (lm)	345
Peak intensity (cd)	900
Adjustable chromaticity	No

REfLED ES50

RefLED ES50 V2 DIM 345LM 830 36° SL

0026592

Electrical data

kWh per 1000 hours burning time	6
Efficacy (Rated) (lm/w)	58
Watt (Nominal) (W)	6.0
Watt (Rated) (W)	6.0
Equivalent watt (W)	50
Voltage (V)	220-240
Current (A)	0.029
Lamp power factor	0.90

Physical data

Lamp Length (mm) - C/L	54
Max. Lamp Diameter (mm) - D	50
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No
Fluorescent lamp replacement	No