

# #5215 - 6 way line Cord, 200m reel

**Part NO:** #5215

**Product Code:** RGW-1858

**Product Description**

**Application:**

For communication and signal control systems.

**Reference Standard**

Customer's sample spec.and the general standard

**Multi-construction**

6

**Cable Construction**

<b>Conductor</b>	<b>Tinned Copper</b>
Construction	T0.16±0.005x7
AWG	26
<b>Insulation</b>	<b>PVC</b>
Min.Thickness	0.21
Insulation Dia.(±0.05mm)	0.90
Insulation Color	1;White; 2;Black 3; Red; 4, Green 5, Yellow; 6,Blue
<b>Filler</b>	<b>Chalk</b>
<b>Jacket</b>	<b>PVC</b>
Min.Thickness(mm)	0.85
Dia.(±0.15mm)	7.1×3.0
Jacket Color	Silver Grey(RAL9023)

**Marking**

**No Marking**


**PACKAGING**

200M/Coil

**Revision History**

A0-1

**Design**



**Electrical Characteristics**

Max.Conductor DC Resistance at 20°C ( Ω /Km)	<132
Min.Insulation DC Resistance at 20°C ( M Ω *Km)	>500
Rated Temperature(°C)	-20 to +60
Rated Voltage(V)	150

**RoHS GUIDELINE**

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	/
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	/

**Date:** 2013-01-23

**Page:** 1 / 1

