



CONGO

SUBMERSIBLE & IN-LINE PUMP KIT

LVM-174
12 volt pump kit

LVM-175
24 volt pump kit



- ◆ Pumps fresh water, sea water and diesel
- ◆ Fast diesel refuelling and transfer with no spillage
- ◆ Bilge pump out in tight areas
- ◆ Water transfer; deck showers; and general wash-down
- ◆ Agricultural spraying, carboy and drum emptying and transfer
- ◆ Robust, slim line with clip-on easy clean filter

FLOW RATE:
Flow rate and current reduces as the height to be pumped increases

RECOMMENDED FUSE SIZE:
12 volt – 6 amp
24 volt – 3 amp

WEIGHT: 1.22 Kg

CONNECTIONS: for 19mm (¾") bore hose



- ◆ Up to 32 litres (7 gallons) per minute
- ◆ Suitable for diesel fuel, water, seawater
- ◆ Temperatures up to 80°C
- ◆ Includes 4m lay-flat hose, adjustable spray nozzle, 4m electrical cable with crocodile clips
- ◆ Intermittent duty



Not suitable for pumping petrol, light hydrocarbons, non-aqueous solvents

Doc 666/13