



### Main

|                           |                         |
|---------------------------|-------------------------|
| Range of product          | Harmony XAC             |
| Product or component type | Pendant control station |
| Device short name         | XACA                    |

### Complementary

|   |  |
|---|--|
| Control station type                        | Double insulated   |
| Enclosure material                          | Polypropylene  |
| Electrical circuit type                     | Control circuit  |
| Enclosure type                              | Complete ready for use   |
| Control station composition                 | 4 push-buttons   |
| Connections - terminals                     | Screw clamp terminals 1 x 2.5 mm <sup>2</sup> with or without cable end<br>Screw clamp terminals 2 x 1.5 mm <sup>2</sup> with or without cable end   |
| Protective treatment                        | TH   |
| Ambient air temperature for operation       | -25...70 °C  |
| Ambient air temperature for storage         | -40...70 °C  |
| Vibration resistance                        | 15 gn 10...500 Hz IEC 60068-2-6  |
| Shock resistance                            | 100 gn IEC 60068-2-27  |
| Overvoltage category                        | Class II IEC 61140   |
| IP degree of protection                     | IP65 IEC 60529   |
| IK degree of protection                     | IK08 EN 50102  |
| Mechanical durability                       | 1000000 cycles   |
| Contact code designation                    | A600 AC-15 240 V 3 A IEC 60947-5-1 appendix A<br>A600 AC-15 600 V 1.2 A IEC 60947-5-1 appendix A<br>Q600 DC-13 250 V 0.27 A IEC 60947-5-1 appendix A<br>Q600 DC-13 600 V 0.1 A IEC 60947-5-1 appendix A  |
| [the] conventional enclosed thermal current | 10 A   |
| Short-circuit protection                    | 10 A fuse protection cartridge gG  |
| Rated operational power in W                | 40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C<br>48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C<br>65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications