

Classic ECO Candle

CLECO CAN 230V 28W E14 SV1

0023740



Range features

- 1:1 replacement of Incandescent Candle lamp
- More efficient - more savings
- Up to two times more average life compared to incandescent lamps = 2000 hours
- Excellent colour rendering (CRI = 100)
- Instant illumination
- Sparkling light output
- Less heat generation than incandescent lamp
- Less CO2 emissions
- Identical shape as standard incandescent lamp
- Commercial and domestic application
- 100% dimmable



PRODUCT OVERVIEW

Light colour	828 Homelight
Technology	Halogen
Ordering number	0023740
Average life (Rated) (h)	2000
Energy class	D
Lamp shape	Candle
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E14
Type	Candle ECO
EAN code	5410288237404
CRI (Ra)	100
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	230

Classic ECO Candle

CLECO CAN 230V 28W E14 SV1

0023740

DATA TABLE

General data

Ordering number	0023740
Technology	Halogen
Average life (Rated) (h)	2000
Average life (Nominal) (h)	2000
Energy class	D
Energy saving lamp	No
Lamp shape	Candle
Lamp finish	Clear
Dimmable	Yes
Cap/Base	E14
Type	Candle ECO
EAN code	5410288237404
E-number SE	8355993
Long description	1:1 replacement of Incandescent Candle lamp. More efficient - more savings. Up to two times more average life compared to incandescent lamps = 2000 hours. Excellent colour rendering (CRI = 100). Instant illumination. Sparkling light output. Less heat generation than incandescent lamp. Less CO2 emissions. Identical shape as standard incandescent lamp. Commercial and domestic application. 100% dimmable
Product name	CLECO CAN 230V 28W E14 SV1
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Classic ECO Candle

CLECO CAN 230V 28W E14 SV1

0023740

Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	370
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	370

Electrical data

kWh per 1000 hours burning time	28
Watt (Rated) (W)	28
Watt (Nominal) (W)	28
Equivalent watt (W)	37
Voltage (V)	230
Lamp power factor	1

Physical data


Weight (kg)	0.02
Lamp Length (mm) - C/L	100
Max. Lamp Diameter (mm) - D	36
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	9.80 x 3.50 x 3.50
Inner package dimensions (L x W x H) (cm)	19.00 x 8.00 x 11.00
Inner package net weight (kg)	0.15
Outer package dimensions (L x W x H) (cm)	43.00 x 21.50 x 25.00

Classic ECO Candle

CLECO CAN 230V 28W E14 SV1

0023740

TECHNICAL DRAWINGS



ENERGY LABEL

