

## LC1F400V7

TeSys F contactor - 3P (3 NO) - AC-3 -  $\leq$  440 V  
400 A - coil 400 V AC



### Main

Range	TeSys
Product name	TeSys F
Product or component type	Contacteur
Device short name	LC1F
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Poles description	3P
Pole contact composition	3 NO
[Ue] rated operational voltage	$\leq$ 1000 V AC 50/60 Hz $\leq$ 460 V DC
[Ie] rated operational current	500 A ( $\leq$ 40 °C) at $\leq$ 440 V AC AC-1 400 A ( $\leq$ 55 °C) at $\leq$ 440 V AC AC-3
Motor power kW	110 kW at 220...230 V AC 50/60 Hz 185 kW at 1000 V AC 50/60 Hz 200 kW at 380...400 V AC 50/60 Hz 220 kW at 415 V AC 50/60 Hz 250 kW at 440 V AC 50/60 Hz 257 kW at 500 V AC 50/60 Hz 280 kW at 660...690 V AC 50/60 Hz
Control circuit type	AC 40...400 Hz
Control circuit voltage	400 V AC 40...400 Hz
[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	500 A at $\leq$ 40 °C
Irms rated making capacity	4000 A AC conforming to IEC 60947-4-1
Rated breaking capacity	3200 kA conforming to IEC 60947-4-1
[Icw] rated short-time withstand current	3600 A $\leq$ 40 °C 10 s 2400 A $\leq$ 40 °C 30 s 1700 A $\leq$ 40 °C 1 min 1200 A $\leq$ 40 °C 3 min 1000 A $\leq$ 40 °C 10 min
Associated fuse rating	400 A aM at $\leq$ 440 V 500 A gG at $\leq$ 440 V
Average impedance	0.26 mOhm at 50 Hz - Ith 500 A
[Ui] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power dissipation per pole	42 W AC-3 65 W AC-1
Mounting support	Plate
Standards	EN 60947-1 EN 60947-4-1 IEC 60947-1 IEC 60947-4-1 JEM 1038
Product certifications	BV CCC CSA DNV GL RINA RMRoS

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

	UL LROS
Connections - terminals	Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit : lugs-ring terminals 2 cable(s) 150 mm <sup>2</sup> Power circuit : bar 2 x ( 30 x 5 mm)
Tightening torque	Power circuit : 35 N.m Control circuit : 1.2 N.m
Operating time	100...170 ms opening 40...65 ms closing
Mechanical durability	10 Mcycles
Operating rate	2400 cyc/h at <= 55 °C

## Complementary

Control circuit voltage limits	0.85...1.1 Uc at 55 °C operational 40...400 Hz 0.3...0.5 Uc at 55 °C drop-out 40...400 Hz
Inrush power in VA	1075 VA at 20 °C (cos $\phi$ 0.9) 40...400 Hz
Hold-in power consumption in VA	15 VA at 20 °C (cos $\phi$ 0.9) 40...400 Hz
Heat dissipation	14 W

## Environment

IP degree of protection	IP20 front face with shrouds (ordered separately) conforming to IEC 60529 IP20 front face with shrouds (ordered separately) conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C
Operating altitude	3000 m without derating in temperature
Mechanical robustness	Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 6 Gn for 11 ms Vibrations contactor closed 5 Gn, 5...300 Hz Vibrations contactor open 1.5 Gn, 5...300 Hz
Height	206 mm
Width	213 mm
Depth	219 mm
Product weight	9.1 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0843 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available