

## XCSDMC5912

coded magnetic switch XCSDMC - 1 NC + 1 NO - staggered - 2m



### Main

Range of product	Preventa Safety detection
Product or component type	Coded magnetic switch
Component name	XCSDMC
Design	Rectangular, compact
Size	51 x 16 x 7 mm
Contacts type and composition	1 NC + 1 NO
Contacts operation	Staggered
Material	Plastic
Electrical connection	Pre-cabled
Cable composition	4 x 0.25 mm <sup>2</sup>
Cable length	2 m
Number of poles	2
Local signalling	1 LED
Approach directions	3 directions
[Ue] rated operational voltage	24 V DC
[Ui] rated insulation voltage	100 V DC

### Complementary

[Sa] assured operating distance	5 mm
[Sar] assured tripping distance	15 mm
[Ie] rated operational current	<= 100 A
[Uimp] rated impulse withstand voltage	2.5 kV conforming to EN/IEC 60947-5-1
Resistance across terminals	57 Ohm
Short circuit protection	500 mA external cartridge fuse type gG (gl)
Contacts material	Rhodium
Electrical durability	1200000 cycles
Maximum switching voltage	DC
Switching capacity in mA	5...100 mA
Insulation resistance	1000 MOhm
Breaking capacity	<= 3 VA
Switching frequency	150 Hz
Safety level	Can reach category 4 (with the appropriate monitoring system and correctly wired) conforming to EN/ISO 13849-1 Can reach PL = e (with the appropriate monitoring system and correctly wired) conforming to EN/ISO 13849-1 Can reach SIL 3 (with the appropriate monitoring system and correctly wired) conforming to EN/IEC 61508
Safety reliability data	B10d = 50000000 (value given for a life time of 20 years limited by mechanical or contact wear)
Enclosure material	Thermoplastic PBT
Cable material	PVC
Depth	7 mm
Height	51 mm
Width	16 mm
Product weight	0.101 kg

### Environment

Standards	EN 1088 EN/IEC 60204-1
-----------	---------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

EN/IEC 60947-5-1  
EN/ISO 12100  
ISO 14119  
UL 508  
CSA C22.2 No 14

Product certifications	BG CSA UL
Protective treatment	TH
Ambient air temperature for operation	-25...85 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	10 gn (f = 10...150 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn for 11 ms conforming to IEC 60068-2-27
Sensitivity to magnetic fields	>= 0.3 mT
Class of protection against electric shock	Class II conforming to IEC 60536
IP degree of protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0729 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold