

# 79 02 125

## Precision Electronics Diagonal Cutter





- precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- approx. 20 % lighter than conventional electronics pliers
- bolted joint with particularly carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- smooth-running double spring for a gentle and even opening
- ergonomically optimised multi- component handles
- forged from chrome vanadium ball-bearing steel
- round head

### The subtle difference

KNIPEX precision electronics pliers are made of high-quality ball bearing steel and processed with the highest degree of care. Each opening movement is gentle and even without backlash. Each work step proceeds reliably and precisely. This makes work much easier for professionals.

Article No.	79 02 125
EAN	4003773061281
Pliers	burnished
Head	polished
Handles	with multi-component grips
Style	0
medium hard wire Ø mm	1,3
hard wire Ø mm	0,7
soft wire Ø mm	0,2 - 1,7
B mm	10
D mm	6,5
A mm	11
Nominal size	125 mm
Length mm	125
Net weight g	59



technical change and errors excepted

