

## Lynx-L

LYNX-L 24W/840 10-WAY

0025657



### Range features



### PRODUCT OVERVIEW

Ordering number	0025657
Light colour	840
Technology	Compact Fluorescent
Energy class	A
Average life (Rated) (h)	16000
Lamp shape	Stick
Dimmable	Referring to ballast
Cap/Base	2G11
Type	Lynx L
EAN code	5410288256573
CRI (Ra)	82
Colour temperature (K)	4000
Luminous flux (Rated) (lm)	1800
Efficacy (Rated) (lm/w)	75
Watt (Nominal) (W)	24
Voltage (V)	87

## Lynx-L

LYNX-L 24W/840 10-WAY

0025657

### DATA TABLE

#### General data

<b>Technology</b>	Compact Fluorescent
<b>Ordering number</b>	0025657
<b>Average life (Rated) (h)</b>	16000
<b>Average life (Nominal) (h)</b>	16000
<b>Energy class</b>	A
<b>Lamp shape</b>	Stick
<b>Dimmable</b>	Referring to ballast
<b>Cap/Base</b>	2G11
<b>Type</b>	Lynx L
<b>EAN code</b>	5410288256573
<b>E-number FI</b>	4940228
<b>Product name</b>	LYNX-L 24W/840 10-WAY
<b>Lamp mercury content (mg)</b>	<2.5
<b>Starting time (max) (s)</b>	<10
<b>Warm-up time to 60% of full light (max) (s)</b>	60
<b>Control gear required</b>	Yes
<b>IEC Reference</b>	IEC 60901
<b>IEC Reference 2</b>	IEC 61199
<b>Intended purpose</b>	General lighting
<b>Special purpose lamp</b>	No
<b>Transformer required</b>	Managtic ballast
<b>Sales pack quantity</b>	10
<b>Rated survival factor at 2000 h 50Hz</b>	0.98
<b>Rated survival factor at 4000 h 50Hz</b>	0.9
<b>Rated survival factor at 6000 h 50Hz</b>	0.85
<b>Rated survival factor at 8000 h 50Hz</b>	0.8
<b>Rated survival factor at 12000 h 50Hz</b>	0.78
<b>Rated survival factor at 16000 h 50Hz</b>	0.5

## Lynx-L

LYNX-L 24W/840 10-WAY

0025657

### Optical data

Light colour	840
CRI (Ra)	82
Colour temperature (K)	4000
Luminous flux (Rated) (lm)	1800
Luminous flux (Nominal) (lm)	1800
Ambient temperature for maximum luminous flux (°C)	25
Rated lumen maint. factor at 2000 h 50Hz	8500%
Rated lumen maint. factor at 4000 h 50Hz	7800%
Rated lumen maint. factor at 6000 h 50Hz	7600%
Rated lumen maint. factor at 8000 h 50Hz	7500%
Rated lumen maint. factor at 12000 h 50Hz	73
Rated lumen maint. factor at 16000 h 50Hz	70

### Electrical data

kWh per 1000 hours burning time	26
Efficacy (Rated) (lm/w)	75
Watt (Rated) (W)	24
Watt (Nominal) (W)	24
Voltage (V)	87
Ignition voltage (V)	198
Current (A)	0.345

### Physical data

Weight (kg)	0.09
Length base to base (mm) - A	No
Lamp Length (mm) - C/L	322.4
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	33.70 x 4.50 x 2.50
Inner package dimensions (L x W x H) (cm)	34.70 x 10.00 x 14.00
Inner package net weight (kg)	0.90
Outer package dimensions (L x W x H) (cm)	53.00 x 37.00 x 16.50


## Lynx-L

LYNX-L 24W/840 10-WAY

0025657

### TECHNICAL DRAWINGS

2G11



### ENERGY LABEL

