

ToLEDo GLS

ToLEDo GLS V2 6.5W 470LM 827 B22 SL

0026674



Range features

- Wide beam angle of 220 degrees!
- Instant start
- Long lifetime 15,000 hours
- Short payback period
- Up to 85% energy savings compared to incandescent equivalent

LED

PRODUCT OVERVIEW

Light colour	Homelight
Technology	LED
Ordering number	0026674
Average life (Rated) (h)	15000
Energy class	A+
Lamp shape	A60
Lamp finish	Frosted
Dimmable	No
Cap/Base	B22
Type	ToLEDo GLS
EAN code	5410288266749
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	470
Efficacy (Rated) (lm/w)	72.3
Watt (Nominal) (W)	6.5
Equivalent watt (W)	40
Voltage (V)	220-240
Colour	Homelight

ToLEDo GLS

ToLEDo GLS V2 6.5W 470LM 827 B22 SL

0026674

DATA TABLE

General data

Dry applications use only	Yes
Technology	LED
Ordering number	0026674
Energy class	A+
Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000
Energy saving lamp	Yes
Lamp finish	Frosted
Lamp shape	A60
Dimmable	No
Cap/Base	B22
Type	ToLEDo GLS
EAN code	5410288266749
Range features	Wide beam angle of 220 degrees! Instant start. Long lifetime 15,000 hours. Short payback period. Up to 85% energy savings compared to incandescent equivalent
Product name	ToLEDo GLS V2 6.5W 470LM 827 B22 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Control gear availability	No
Intended purpose	No
No. of switching cycles before premature failure (min)	20000
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

Optical data

Light colour	Homelight
CRI (Ra)	80
Suitable for accent lighting	No
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	470
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	470
Adjustable chromaticity	No

ToLEDo GLS

ToLEDo GLS V2 6.5W 470LM 827 B22 SL

0026674

Electrical data

kWh per 1000 hours burning time	7
Efficacy (Rated) (lm/w)	72.3
Watt (Nominal) (W)	6.5
Watt (Rated) (W)	6.5
Equivalent watt (W)	40
Voltage (V)	220-240
Current (A)	36
Lamp power factor	0.8

Physical data

Colour	Homelight
Lamp Length (mm) - C/L	108
Max. Lamp Diameter (mm) - D	60
Lamp dimension equal to filament lamp equivalent	Yes
Diameter (mm)	60

ENERGY LABEL

