



The company named below has been authorized by Canadian Standards Association to represent the products listed in this record as "CSA Certified" or "CSA Accepted", as applicable, and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

NUMBR 004442TC000 March 2, 1995(Replaces:June 30, 1994)

CLASS 6241 10 (Re-examination Service - Category Certification)

MICRO SWITCH

4442C

A Div. of Honeywell Inc.

11 W. Spring St.

Freeport, IL 61032

SEE ALSO NRTL

FACTORIES

1. A Div. of Honeywell Inc. - (F1 MASTER)

11 W. Spring St.

Freeport, IL 61032

2. A Div. of Honeywell Inc. - (F2 MASTER)

323 E. Stephenson St.

Freeport, IL 61032

SEE ALSO SATELLITE FACTORY FILE LR 103707 AND LR 41372.

SWITCHES - Snap - Special Use

THE FOLLOWING COMPLY WITH CSA STD C22.2 No 55-M1986:

- Cat No DB-RH with suffix numerals 2-7 incl., dpdt.

- Code No L-1, 15A, 125, 250 or 480V ac.

- Type DM, single-pole, single- and double-throw, Code No L22, 1A, 125V ac, L93, 10A, 125-250V ac, 1/3 hp, 125 or 250V ac, Code L157, 10A, 1/3 hp, 125, 250 or 277V ac, Code L181, 10A, 1/2 hp, 125, 250, 277V ac, Code L226, 5A, 125-250V ac, Code No 263, 10A, 1/2 hp, 125, 250, 277V ac, 2A, 24V dc, Cat No 1DM, 2DM, 3DM, 4DM, 13DM, 14DM, with suffixes 1 to 1000, with or without letters A to Z; with or without numbers designating customer part number, type of terminal, angle of terminal or degree of overtravel.

- Type 2DM600, Circuit 1, Code L229, 0.1A, 125V, 1/10 hp, 125V ac, Circuit 2, Code L230, 0.1A, 125V.

- Lighted Types DM, SPDT or SPST, Code No L93, 10A, 125-250V ac, 1/3 hp, 125 or 250V ac.

- Type HS, Code L22, 1A, 125V ac, Code L244, 1A, 125V ac, 28V dc, Code L277, 1A, 125V ac; 5A, 28V dc, Cat Nos 1HS, 4 HS, 101HS, 102HS, Code L267, 5A, 28V dc, with or without suffix numbers.

- Type HT, Code L110, 3A, 125/250V ac, 1/1 hp, 125V ac, 1/6 hp, 250V ac, with prefix numbers 1, 2, 3 or 4 and suffix numbers 1 to 1000, may be used to 1000F.

- Type 4SE, Code L4, 5A, 250V ac, Cat Nos 4SE1, 4SE2, 4SE3, 47SE1, with or without suffix numbers; Code L151, 5A, 250V ac, 5A, 30V dc, Cat No 4SE151.

- Type TK with prefix and suffix numbers.

- Code L191, 15A, 125, 250 or 277V ac, 5A, 125V ac (tungsten), 1/2 hp, 125V ac, 1 hp, 250 or 277V ac.

- Code L192, 10A, 125, 250 or 277V ac, 3A, 125V ac (tungsten), 1/4 hp, 125V ac, 1/2 hp, 250 or 277V ac.



The company named below has been authorized by Canadian Standards Association to represent the products listed in this record as "CSA Certified" or "CSA Accepted", as applicable, and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

004442T0000 March 2, 1995(Replaces: June 30, 1994)

CLASS 6241 10 (Re-examination Service - Category Certification)

Page 2

- Type TS with prefix 1 or 3 followed by 1, 2, 3 or 4.
- Code L54, 15A, 125-250V ac, 1/3 hp, 125V ac, 3/4 hp, 250V ac, 1/2A, 125V dc, 1/4A, 250V dc.
- Code L55, 15A, 125-250V ac, 1/2 hp, 125V ac, 1 hp, 250V ac, 1/2A, 125V dc, 1/4A, 250V dc.
- Code L191, 15A, 125-277V ac, 5A, 125V ac (tungsten), 1/2 hp, 125V ac, 1 hp, 250-277V ac.
- Code L192, 10A, 125-277V ac, 3A, 125V ac (Tungsten), 1/4 hp, 125V ac, 1/2 hp, 250-277V ac.
- Prefix numeral 2 (e.g. Cat No 212TS15-1), indicates a switch provided with a panel mounting seal. Prefix numeral 5 (e.g. 512TS15-1) indicates a neoprene seal on the toggle. Suffix numeral 95 immediately following "11TS" or "12TS" indicates a switch with quick-disconnect type male terminals to accept either "AMP" or "ARK-LES" female solderless quick-disconnect wire connectors.
- Type XL, Cat No 37XL, 5V dc, 20mA dc; Cat No 47XL, 6 to 16V dc, 40mA dc.
- Type VX, 4.5 to 24V dc, 0.015A max.
- Lighted pushbutton, Series 2 with suffixes, rating codes of component switches, Series 4, followed by suffixes, Code L22, 1A, 125V ac; Code L4, 5A, 250V ac; Code L99, 10A, 1/4 hp, 125 or 250V ac.
- Types NR, NT, TP, TL, Code L191, 15A, 125/250/277V ac, 1/2 hp, 125V ac, 1 hp, 250V ac, 5A, 125V ac (tungsten); Code L192, 10A, 125/250/277V ac, 1/4 hp, 125V ac, 1/2 hp, 250V ac, 3A, 125V ac (tungsten).
- Type TW, Code L117, 5A, 125V ac.
- AML10 Series, electronic switch for use in business machines, lighted or unlighted, electrical rating 40mA max, 16V dc max; pushbutton, ALM11, 12 with suffixes paddle or rocker, AML13, 14, 15, 16 with suffixes.
- AML20 Series lighted or unlighted, Code L173, 3A, 125V ac 2A, 250V ac, Code L203, 0.1A, 125V; pushbutton AML21, 22 with suffixes; paddle or rocker AML23, 24, 25, 26 with suffixes, AML27, Code L173, 3A, 125V ac, 2A, 250V ac, Code L203, 0.1A, 125V dc.
- AML21 Series, Cat No AML21BAZCD-001, lighted, with 2 poles rated code L173, 3A, 125V ac, two poles rated code L203, 0.1A, 125V ac.
- AML30 Series, lighted or unlighted pushbutton AML31, 32 with suffixes, Code L29, 10A, 250V ac, Code L93, 10A, 125-250V ac, 1/3 hp, 125-250V ac; paddle or rocker AML33, 34, 35, 36 with suffixes, Code L186, 15A, 125-250V ac.
- Series MML31, MML83 with suffixes, 6A, 125-250V ac, 2A, 30V dc, 1A, 125V ac (tungsten), 1/10 hp, 125V ac.
- Series MML33 and MML34 with suffixes, single or double-pole, single-throw, 6A, 125V ac; 4A, 250V ac; 2A, 30V dc; 1A, 125V ac (tungsten); 1/10 hp, 125V ac.

(Cont'd)