




RECOMMENDED PC BOARD LAYOUT

0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200]
FROM MATING END, 3.81um [.000150] MIN TIN FOR A
LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH
OVER 1.27um [.000050] MIN NICKEL.

OBsolete PARTS: OBsolete CIS STREAMLINING PER D.RENAUD/D.SINISI

		YES	 1-207120-2
		NO	1-207120-1
		NO	1-207120-0
		YES	207120-9
		YES	207120-8
2		YES	 207120-7
		NO	207120-4
		YES	207120-3
		NO	207120-2
		YES	207120-1
	CONTACT FINISH	MOUNTING TABS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE	03/11/92		 TE Connectivity			
		CHK R.STONE	3-17-92					
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	NAME PIN HEADER ASSEMBLY, 12 POSITION, METRIMATE —					
		PRODUCT SPEC 108-10033						
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C-207120	RESTRICTED TO —		
		MATERIAL	FINISH	WEIGHT —				
HOUSING: 1	CONTACT: SEE TABLE	CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1	REV S2