

Printed-circuit board connector - MSTBO 2,5/ 3-G1PR BK - 2200488

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Header, Nominal current: 12 A, Rated voltage (III/2): 320 V, Number of positions: 3, Pitch: 5 mm, Mounting: Soldering, Article with lateral pin exit

The illustration shows the version in gray



Key commercial data

Packing unit	1
GTIN	 4 046356 657280
Custom tariff number	85366990

Technical data

Dimensions

Pitch	5 mm
-------	------

General

Range of articles	MSTBO 2,5/..-G1PL
Rated surge voltage (III/3)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (II/2)	4 kV
Rated voltage (III/3)	250 V
Rated voltage (III/2)	320 V
Rated voltage (II/2)	400 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	12 A
Insulating material	PA
Number of positions	3

Printed-circuit board connector - MSTBO 2,5/ 3-G1PR BK - 2200488

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 4.0	EC002637
ETIM 5.0	EC002637

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals


Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals


Approvals submitted


Approval details

UL Recognized 		
	B	D
Nominal current I _N	12 A	12 A
Nominal voltage U _N	250 V	150 V

Printed-circuit board connector - MSTBO 2,5/ 3-G1PR BK - 2200488

Approvals

cUL Recognized 		
	B	D
Nominal current I _N	12 A	12 A
Nominal voltage U _N	250 V	150 V

cULus Recognized 		
--	--	--